









版次 (Edition)	变更摘要 (Change The Content)	日期 (Date)
0	新产品发行 (The first edition)	2022/12/19
1	料号更新 (Material number update)	2024/12/06

序号 (NO.)	品名 (TITLE)	材质 (Material)
①	1.25A型双排立式端子 1.25 Type A Double row S/T Terminal	黄铜/表面镀锡80u"Min, 镀锡30u"Min Brass/Tin-coated surface 80u" Min, Nickel-plated 30u"Min
②	1.25A型双排立式焊片1.25 Type A Double row S/T Solder tab	黄铜/表面镀锡80u"Min, 镀锡30u"Min Brass/Tin-coated surface 80u" Min, Nickel-plated 30u"Min
③	1.25A型双排立式胶芯 1.25 Type A Double row S/T Housing	PA6T UL94V-0 本色 Natural
④	1.25A型双排立式吸盖 1.25 Type A Double row S/T Cover	LCP UL94V-0 本色 Natural



技术指标 (Technical Index):

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
- 温度范围 (Temperature range): -25° C ~ +85° C.
- 额定电压 (Rated voltage): 150V, AC/DC.
- 额定电流 (Rated current): 1.0A AC/DC (AWG#28).
- 接触电阻 (Contact resistance): ≤20mΩ (Initial) per contact, ≤40mΩ Change allowed.
- 绝缘电阻 (Insulation resistance): ≥500MΩ.
- 耐电压 (Withstanding Voltage): 500V AC (Minute)
- 产品料号 (Product material No.):

WB125A1T-**-**-****

NO OF CKT (产品PIN数)

流水码
(Serial number)

Plating (电镀方式)

- 端子全金
(Terminal all fog tin)
- 端子全亮锡
(Terminal all bright tin)

Packing (包装方式)

- R: TAPE & REEL 卷装
C: TAPE & REEL WITH COVER
加吸盖卷装

CKT	A	B
2*5	12.50	5.00
2*6	13.75	6.25
2*7	15.00	7.50
2*8	16.25	8.75
2*9	17.50	10.00
2*10	18.75	11.25
2*11	20.00	12.50
2*12	21.25	13.75
2*13	22.50	15.00
2*14	23.75	16.25
2*15	25.00	17.50
2*16	26.25	18.75
2*17	27.50	20.00
2*18	28.75	21.25
2*19	30.00	22.50
2*20	31.25	23.75
2*21	32.50	25.00
2*22	33.75	26.25
2*23	35.00	27.50
2*24	36.25	28.75
2*25	37.50	30.00



一般公差 (TOLERANCE)
X. ±.50 .XX ±.10
X. ±.20 .XXX ±.05
ANGLES ±1°

ZGWD 浙江温达电子有限公司 ZHEJIANG WENDA ELECTRONICS CO., LTD		制图 (DR)	审核 (APPD)
品名 (TITLE) 1.25 Pitch A型 (DF13) 双排立式带柱 1.25 Pitch Type-A (DF13) Double row S/T WTB With columns		Anlan	田峰
料号 (DWG.NO) WB125A1T-****-****		校对 (CHKD)	黄志明
比例 (SCALE)	单位 (UNITS) mm	张数 (SHEET) 1 OF 1	SIZE A4