





Circuit diagram



PCB Layout(Pattern Side)



Product No. : TS-092S-□□□□

型号:

└─: 包装方式

-P=编带(非编带, 不启用)

操作力度：

120=120gf±50gf

$$180 = 180_{gf} \pm 50_{gf}$$
$$250 = 250gf \pm 50gf$$

—:按钮颜色

-W=白色

一:弹片

D2=SUS/1PCS

D4=SUS/2PCS

Ⓕ	Dust film		1	Polyimide tape	
Ⓔ	Terminal		2	Brass	Silvering
Ⓓ	Reed		1	SUS	Silver covered
Ⓒ	Base		1	PPA	Black
Ⓑ	Cover		1	SUS	
Ⓐ	Button		1	PPA	White
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
— 众迪 —

® Zhongdi Electronic Technology Co., Ltd

design	
--------	--

date		name	TACT SWITCHES
------	--	------	---------------

Review	
Approved	

	date		name	FACT SWITCHS
	date			

Approved _____
number: _____

date	model	TS-092S-□D□-W
------	-------	---------------

Drawing number:	
-----------------	--

ed	Proportion	1:1
----	------------	-----

	1
--	---

unit

mm

m	g
---	---

ape n

number

--	--

--	--

A4

中

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械 性能 Mechanical Properties	机械寿命 Mechanical life:	50,000 cycles Min
	操作行程 Operation Stroke:	0.25±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等。 Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd																			
design			date			name			TACT SWITCHS																				
Review			date			model			TS-092S-□D□-W																				
Approved			date																										
number:																													
1:1			unit		mm		gape number														A4								