







RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATESPECIFICATION
MATERIAL

See drawing

STANDARD DATA

Rating current:1.5A

ELECTRICAL

Insulator resistance: 100M ohms Min

Withstanding voltage: 100 VAC / minute

Contact resistance: 40 m ohms Max

MECHANICAL

Mating force: 5~20N.

Unmating force: 8~20N.

Durability: 10000 cycles Min.

PART NO.

ITEM 項目	PARTS NAME 零件名稱	Q'TY 數量	MATERIAL 材質	FINISH/REMARK 處理/備註
1	Insermold housing	1	SYNTHETIC RESIN	Black
2	12pin Insermold-(1)	1	SYNTHETIC RESIN	Black
3	12pin Insermold-(2)	1	SYNTHETIC RESIN	Black
4	SHELL	1	STAINLESS	Ni:50u" Min
5	12pin Contact-(DIP)	12	COPPER ALLOY	Gold flash on contact area 100u" Tin on solder tails, base Nickel:50u"
6	12pin Contact-(SMT)	12	COPPER ALLOY	Gold flash on contact area 100u" Tin on solder tails, base Nickel:50u"
7	Shield SHELL	1	STAINLESS	base Nickel:50u" Min :Tic:80u" Min Over All
8		1	STAINLESS	Ni:50u" Min
9	Ground plate-bottom	1	STAINLESS	Ni:50u" Min

Signal Name	GND	SSRXp1	SSRXn1	VBUS	SBU2	Dn2	Dp2	CC2	VBUS	SSTXn2	SSTXp2	GND
PIN	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
Signal Name	GND	SSTXp1	SSTXn1	VBUS	CC1	Dp1	Dn1	SBU1	VBUS	SSRXn2	SSRXp2	GND
PIN	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	918-418K2024C40201
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	TYPE-C3.1 24P沉板1.98母座L10.3六脚 插板LCP黑胶端子DIP+SMT
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	版本 VER

RoHS


目錄
MAPX

設定內容
MODIFICATION

日期
DATE

ITEM 項目	PARTS NAME 零件名稱	FINISH/REMARK 處理/備註
1	CONNECTOR	12000 PCS/BOX
2	BOX	12 REEL/BOX
3	WATERPROOF BAG	1 PCS
4	REEL	1000 PCS/REEL
5	COVER TAPE	Wide=24mm
6	CARRIER TAPE	---
7	LABEL	批號標籤

TOP COVER TAPE



- NOTES
- 1.MATERIAL: PS (Color: 透明)
 - 2.DEFORMATION(變形)&DAMAGE(損壞): NA.(不可)
 - 3.All dimensions meet EIA-481-C requirements.

产品图
PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

單位 UNITS	MM	制圖 DRAWING	Erick	產品料號 PRODUCT PART NO.
比例 SCALE	1:1	審核 CHKD	L S S	產品名稱 PRODUCT NO.
日期 DATE	2021/03/10	核准 APPD	黃國榮	角法 VIEW



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

TAPE REEL成品擺放方向

您正在使用 ZWCAD 2022 个人版，不得用于商业用途，详情请咨询 4007-182-588。