




CUSTOMER DRAWING



CIRCUIT



MARKING

HAOTONG  
H25-0322PC  
3(3)A 125/250VAC

| H25 Series | 03 Rating                       | XX Function                      | X Terminal Type                    | X Actuator Type         | X Actuator Height       | X Housing Type | X Terminal Type            | X Actuator Color            | X Housing Color             | XX Suffix |
|------------|---------------------------------|----------------------------------|------------------------------------|-------------------------|-------------------------|----------------|----------------------------|-----------------------------|-----------------------------|-----------|
| 03         | 10A 125VAC<br>(0.3A 125/250VAC) | 12 ● ○<br>13 ● ○ ○<br>14 ● ○ ○ ○ | S Scale Terminal<br>P PC4 Terminal | A 3mm<br>B 4mm<br>C 5mm | 3 3mm<br>4 4mm<br>5 5mm | N<br>R         | T1<br>T2<br>T3<br>T4<br>T5 | B Black<br>W White<br>R Red | B Black<br>W White<br>R Red |           |
| ...        | ...                             | ...                              | ...                                | ...                     | ...                     | ...            | ...                        | ...                         | ...                         | ...       |
| 22         | ...                             | ...                              | ...                                | ...                     | ...                     | ...            | ...                        | ...                         | ...                         | ...       |
| 23         | ...                             | ...                              | ...                                | ...                     | ...                     | ...            | ...                        | ...                         | ...                         | ...       |
| 24         | ...                             | ...                              | ...                                | ...                     | ...                     | ...            | ...                        | ...                         | ...                         | ...       |

规格 Specification:

- 1.开关型号 Model No.:H25-0322PC
- 2.额定值 Rating:3(3)A 125/250VAC
- 3.接触电阻 Contact resistance:≤30 mΩ
- 4.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 5.电气寿命 Electronics life: > 10000 cycles
- 6.操作力 Operation force:500±150gf
- 7.所有材料符合Rohs要求 All materials are Rohs compliant



佛山市皓通电子有限公司  
Foshan Haoswitch Electronic Co.,Ltd.

| DRAWN BY    | 制 图   | APLIN                            | 2026/01/08         | SCALE     | FREE         | PRODUCT NAME | 产品名称 | SLIDE SWITCH |
|-------------|-------|----------------------------------|--------------------|-----------|--------------|--------------|------|--------------|
| CHECKED BY  | 核 对   | APLIN                            | 2026/01/08         | PAGE      | 1/1          | DESCRIPTION  | 产品描述 |              |
| APPROVED BY | 批 准   | ZHANG                            | 2026/01/08         | UNIT      | mm           | PART NO.     | 物料编号 |              |
| TOLERANCE   | 未标注公差 | X: ±0.5<br>X': ±0.3<br>.XX: ±0.2 | X': ±5°<br>X': ±2° | PROJECTED | 投影           |              |      |              |
|             |       |                                  |                    | SIZE      | A4           |              |      |              |
|             |       |                                  |                    | DRAWN NO. |              |              |      |              |
|             |       |                                  |                    | HTDWN     | 20260108-210 |              |      |              |