

CUSTOMER DRAWING

F		G		H	
REV.	ECN NO.	DATE	DESCRIPTION	APPROVED BY	
版本	ECN编号	日期	内容描述	核准	
A0	—	2026/01/08	NEW RELEASE	APLIN	



Technical drawing of a rectangular plate with a central slot. The overall width is 10.5. The overall height is 16.1. The central slot has a width of 0.7 + 0.2. The slot is divided into three sections: a top section with horizontal lines, a middle section with a cross-hatch pattern, and a bottom section with a grid pattern. There are four circular holes on each long side of the plate, two on each side of the central slot.

PCB LAYOUT

H25	03	XX	X	X	X	X	X	X	XX	
Series	Rating	Function	Terminal Type	Actuator Type	Actuator Height	Housing Type	Terminal Type	Actuator Color	Housing Color	Suffix
03	10A 125VAC 6A 250VAC 6(3)A 125/250VAC	12  	S	A 	3 3mm	N 	T1 	B Black	B Black	
		13    	P	Pc3 Terminal	4 4mm		W White	W White		
		14     			5 5mm	R 	T2 	R Red	R Red	
		...	...	...		C 	...		T3 	
22		   								
23		    								
24		     								
...	...						T4 			
...	...						T5 			

规格 Specification:

1. 开关型号 Model No.:H25-0322PC
2. 额定值 Rating:3(3)A 125/250VAC
3. 接触电阻 Contact resistance:≤30 mΩ
4. 绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
5. 电气寿命 Electronics life: > 10000 cycles
6. 操作力 Operation force:400±150gf
7. 所有材料符合Rohs要求 All materials are Rohs compliant
8. 出厂使用需知: 30天之后使用, 需烘烤6个小时, 温度110℃, 再进行使用 (尼龙91特性), 样品需要手焊。



MARKING



CIRCUIT

HAOSWITCH									
佛山市皓通电子有限公司 Foshan Haoswitch Electronic Co.,Ltd.									
DRAWN BY 制 图	APLIN	2026/01/08	SCALE 比 例	FREE	PRODUCT NAME 产 品 名 称 SLIDE SWITCH				
CHECKED BY 核 对	APLIN	2026/01/08	PAGE 页 面	1/1					
APPROVED BY 批 准	ZHANG	2026/01/08	UNIT 单 位	mm					
X: ±0.5 X: ±0.3 .XX: ±0.2		X': ±5° X': ±2°							
TOLERANCE 未标注公差		SIZE 尺 寸			A4				
DRAWING NO. 图纸编号		H2S-0322PC-SNT12ZWV-16A							
					HTDDW20260108-552				