

CUSTOMER DRAWING

H25 Series
Iron Housing Rating Function Terminal Type Actuator Type Actuator Height Housing Type Versions Progress Buttons Colors Suffixes

Isometric View

Top View

Schematic Diagram

P.C.B Layout


规格 Specification:
1.型号 Model:H25
2.额定值 Rating:3A 125VAC/1A 250VAC
2.接触电阻 Contact resistance:≤100 mΩ
3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
4.使用寿命 Operation life:>5000 cycles(Unloading)
5.操作力 Operation force:600±200gf
6.所有材料符合Rohs要求 All materials are Rohs compliant

Haoswith®
佛山市皓通电子有限公司
FoShan Haoswitch Electronic Co.,Ltd.


DRAWN BY图制	APLIN	2026/01/08	SCALE比例	FREE	PRODUCT NAME产品名称	SLIDE SWITCH		
CHECKED BY核对	APLIN	2026/01/08	PAGE页面	1/1	DESCRIPTION产品描述	2P3T 3A 125VAC/1A 250VAC		
APPROVED BY批准	ZHANG	2026/01/08	UNIT单位	mm	PART NO.物料编号	H25A-0123PC-12NT1BB		
TOLERANCE未标注公差	X: ±0.5 .X: ±0.3 .XX: ±0.2	.X°: ±5° .X°: ±2°	PROJECTED投影		SIZE尺寸	A4	DRAWN NO.图纸编号	HTDW20260108-066

REV. 版本	ECN NO. ECN编号	DATE 日期	DESCRIPTION 内容描述	APPROVED BY 核准
A0	——	2026/01/08	NEW RELEASE	APLIN

H25	A	01	XX	X	X	X	X	X	X	X	XX	
Series	Iron	Rating	Function	Terminal Type	Actuator Type	Actuator Beadings	Housing Type	Terminal Type	Progress	Actuator Color	Housing Color	Suffix
	01	24 1A 125VAC 250VAC	12	P PCB Terminal	C	3 SMD	N	T1	Z SMD	B Black	B Black	
			13			4 SMD	M		DIP	M White	M White	
			14			5 SMD	M			R Red	M Red	
			15									
			20				S					
			21									
			24				SI					
			25									



SCHEMATIC(SHORTING)



P.C.B LAYOUT

规格 Specification:

- 1.型号 Model: H25
- 2.额定值 Rating:3A 125VAC/1A 250VAC
- 2.接触电阻 Contact resistance:≤100 mΩ
- 3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 4.使用寿命 Operation life:>5000 cycles(Unloading)
- 5.操作力 Operation force:600±200gf
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

Haoswith

佛山市皓通电子有限公司
FoShan Haoswitch Electronic Co.,Ltd.

DRAWN BY 制 图	APLIN	2026/01/08	SCALE 比 例	FREE	PRODUCT NAME 产品名称	SLIDE SWITCH	
CHECKED BY 核 对	APLIN	2026/01/08	PAGE 页 面	1/1	DESCRIPTION 产品描述	2P3T 3A 125VAC/1A 250VAC	
APPROVED BY 批 准	ZHANG	2026/01/08	UNIT 单 位	mm			
TOLERANCE 未标注公差	X: ±0.5 .X: ±0.3 .XX: ±0.2	X°: ±5° .X°: ±2°	PROJECTED 投影 	PART NO. 物料编号	H25A-0123PC-12NT1BB		
				SIZE 尺寸	A4	DRAWN NO. 图纸编号	HTDW20260108-066