

RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATE

NOTES:

MOLDING: LCP UL94 V-0

CONTACT: COPPER ALLOY.

GOLD PLATING ALL OVER 50u" Min NICKEL
AND 100u" Min Tin ALL OVER 50u" Min NICKEL
ON SOLDER AREA

SHELL: SUS304-H, T=0.30±0.03mm

50u" NICKEL PLATING OVER ALL.

SHILD: SUS304-H, T=0.12±0.03mm

INSERTION: 5~20N.

EXTRACTION: 8~20N AFTER TEST .

DURABILITY: 10000 CYCLES

3. ELECTRICAL:

CURRENT: 5A FOR VBUS;

1.25A FOR GND PIN.

0.25A FOR OTHER.

VOLTAGE: 20 V MAX





WITHSTANDING VOLTAGE: 100V AC R.M.S

CONTACT RESISTANCE: 40mΩ MAX.

INSULATION RESISTANCE: 100MΩ MIN.

4. ENVIRONMENTAL

TEMPERATURE RANGE -55°C ~ +85°C



Signal Name	GND	SSRXp1	SSRXn1	Vbus	SBU2	Dn2	Dp2	CC2	Vbus	SSTXn2	SSTXp2	GND
PIN	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
Signal Name	GND	SSTXp1	SSTXn1	Vbus	CC1	Dp1	Dn1	SBU1	Vbus	SSRXn2	SSRXp2	GND
PIN	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE


X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.


单位	MM	制图	Erick	产品料号	918-648K202AF30008
比例	1:1	审核	L S S	产品名称	TYPE-C3.1母座8.8立贴无弹有柱
日期	2021/03/10	核准	黄国荣	产品编号	四脚插板带小脚LCP黑胶24PIN
角法	VIEW	版本	VER	角法	VIEW

您正在使用 ZWCAD 2022 个人版, 不得用于商业用途, 详情请咨询 4007-182-588.


RoHS

目錄
MAPX設 變 內 容
MODIFICATION日 期
DATE



① 胶盘




② 600pcs/盘



③ 10盘/箱(6Kpcs)



⑤ 外箱用透明胶纸带封“工”字型。



④ 每箱装10盘,若尾数箱在空间处加装填充物。

备注:

1. 胶盘规格: 外圆 * 内圆 * 厚: 380*13*22 mm
2. 每箱装 10 盘 (6Kpcs);
3. 外箱尺寸 : 长*宽*高: 39*39*31.0 cm
材质 : A=B ;
4. 外箱用透明胶纸带封 “工” 字型 ;
5. 依外箱图示位置粘贴好产品或 ROHS 标签 .

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.单位
UNITS

MM

制图
DRAWING

Erick

产品料号
PRODUCT PART NO.比例
SCALE

1:1

审核
CHKD

L S S

产品名称
PRODUCT NO.

TYPE C 24P 立贴10.0

日期
DATE

2021/03/10

核准
APPD

黄国荣

角法
VIEW版本
VER

A0