









技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

High photosynthesis 台高(H)	The female seat height 母座半高(H1)	The male seat height 公座半高(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9

Part No	CKT	A	B	C	D	E
BTB0835M-2*4PAL1	2*4	2.40	3.50	5.10	4.20	4.00
BTB0835M-2*5PAL1	2*5	3.20	4.30	5.90	5.00	
BTB0835M-2*6PAL1	2*6	4.00	5.10	6.70	5.80	
BTB0835M-2*7PAL1	2*7	4.80	5.90	7.50	6.60	
BTB0835M-2*8PAL1	2*8	5.60	6.70	8.30	7.40	
BTB0835M-2*9PAL1	2*9	6.40	7.50	9.10	8.20	
BTB0835M-2*10PAL1	2*10	7.20	8.30	9.90	9.00	
BTB0835M-2*11PAL1	2*11	8.00	9.10	10.70	9.80	8.00
BTB0835M-2*12PAL1	2*12	8.80	9.90	11.50	10.60	
BTB0835M-2*13PAL1	2*13	9.60	10.70	12.30	11.40	
BTB0835M-2*14PAL1	2*14	10.40	11.50	13.10	12.20	
BTB0835M-2*15PAL1	2*15	11.20	12.30	13.90	13.00	
BTB0835M-2*16PAL1	2*16	12.00	13.10	14.70	13.80	
BTB0835M-2*17PAL1	2*17	12.80	13.90	15.50	14.60	
BTB0835M-2*18PAL1	2*18	13.6	14.70	16.30	15.40	
BTB0835M-2*19PAL1	2*19	14.40	15.50	17.10	16.20	
BTB0835M-2*20PAL1	2*20	15.20	16.30	17.90	17.00	
BTB0835M-2*22PAL1	2*22	16.80	17.90	19.50	18.60	
BTB0835M-2*25PAL1	2*25	19.20	20.30	21.90	21.00	
BTB0835M-2*30PAL1	2*30	23.20	24.30	25.90	25.00	
BTB0835M-2*35PAL1	2*35	27.20	28.30	29.90	29.00	
BTB0835M-2*40PAL1	2*40	31.20	32.30	33.90	33.00	
BTB0835M-2*50PAL1	2*50	39.20	40.30	41.90	41.00	

序号	品名	材质	TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
			X.±0.50	±1°		PART NO.	TITLE: 0.8 Pitch双槽立式 BTB母座业务图(单高3.5)	
①	0.8 Pitch双槽立式 BTB母座胶芯	PA10T UL94 V-0, 颜色:黑色	X.X±0.20		BTB0835M-2*NPAL1	MANUFACTURE DWG		
②	0.8 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金	X.XX±0.10					
③	0.8 Pitch双槽立式 BTB母座吸盖	LCP UL94 V-0, 颜色:黑色	UNITS	mm	DESIGN: Ethan			
			MATERILA	— — —	CHED: Olvia		SCALE	SHEET
			FINISH	— — —	APPD: Ava		N:A	1/1