









REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



High photosynthesis 合高 (H)	The female seat neight 插座高度 (H1)	The male seat neight 公座高度 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



适用线路板

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$ 。

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTB0540G-2*4PAL1	2*4	1.50	2.50	4.70	3.40	4.00
BTB0540G-2*5PAL1	2*5	2.00	3.00	5.20	3.90	
BTB0540G-2*6PAL1	2*6	2.50	3.50	5.70	4.40	
BTB0540G-2*7PAL1	2*7	3.00	4.00	6.20	4.90	
BTB0540G-2*8PAL1	2*8	3.50	4.50	6.70	5.40	
BTB0540G-2*9PAL1	2*9	4.00	5.00	7.20	5.90	
BTB0540G-2*10PAL1	2*10	4.50	5.50	7.70	6.40	
BTB0540G-2*11PAL1	2*11	5.00	6.00	8.20	6.90	
BTB0540G-2*12PAL1	2*12	5.50	6.50	8.70	7.40	
BTB0540G-2*13PAL1	2*13	6.00	7.00	9.20	7.90	
BTB0540G-2*14PAL1	2*14	6.50	7.50	9.70	8.40	8.00
BTB0540G-2*15PAL1	2*15	7.00	8.00	10.20	8.90	
BTB0540G-2*16PAL1	2*16	7.50	8.50	10.70	9.40	
BTB0540G-2*17PAL1	2*17	8.00	9.00	11.20	9.90	
BTB0540G-2*18PAL1	2*18	8.50	9.50	11.70	10.40	
BTB0540G-2*19PAL1	2*19	9.00	10.00	12.20	10.90	
BTB0540G-2*20PAL1	2*20	9.50	10.50	12.70	11.40	
BTB0540G-2*22PAL1	2*22	10.50	11.50	13.70	12.40	
BTB0540G-2*25PAL1	2*25	12.00	13.00	15.20	13.90	
BTB0540G-2*30PAL1	2*30	14.50	15.50	17.70	16.40	
BTB0540G-2*35PAL1	2*35	17.00	18.00	20.20	18.90	
BTB0540G-2*40PAL1	2*40	19.50	20.50	22.70	21.40	
BTB0540G-2*50PAL1	2*50	24.50	25.50	27.70	26.40	

序号	品名	材质	TOLERANCE	深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
①	0.5 Pitch双槽立式 BTB公座胶芯	PA10T UL94 V-0 颜色:黑色	X:±0.50 X.X±0.20 X.XX±0.10	±1°	PART NO. BTB0540G-2*NPAL1	TITLE: 0.5 Pitch双槽立式BTB公(单高4.0)	
②	0.5 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金	UNITS mm		DESIGN: Ethan	MANUFACTURE DWG	
③	0.5 Pitch双槽立式 BTB公座吸盖	LCP UL94 V-0颜色:黑色.	MATERILA FINISH	— — — — — —	CHED: Olvia APPD: Ava	SCALE N:A	SHEET 1/1