







REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	规格
①	4.2A 垂直式 WTB 插座 4.2A Type Double-row Vertical WTB Housing	LCP UL94V-0 黑色 LCP UL94V-0 Black
②	4.2A 垂直式 WTB 端子 4.2A Type Double-row Vertical WTB Terminal	铜合金/表面镀锡 Copper Alloy/Tin Plating

技术指标:


1. 工作温度 (Temperature range): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压 (Rated voltage): 250V AC, DC.
3. 耐压 (Dielectric withstanding voltage): 1500V AC/minute.
4. 接触电阻 (Contact Resistance): $20\text{m}\Omega$.
5. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.
6. 额定电流 (Rated current): 5A AC, DC.




PCB Layout

Part No	CKT	A	B	C
XY-MX4.2A-4A51	2X2	4.20	9.60	0.00
XY-MX4.2A-6A51	2X3	8.40	13.80	4.20
XY-MX4.2A-8A51	2X4	12.60	18.00	8.40
XY-MX4.2A-10A51	2X5	16.80	22.20	12.60
XY-MX4.2A-12A51	2X6	21.00	26.40	16.80
XY-MX4.2A-14A51	2X7	25.20	30.60	21.00
XY-MX4.2A-16A51	2X8	29.40	34.80	25.20
XY-MX4.2A-18A51	2X9	33.60	39.00	29.40
XY-MX4.2A-20A51	2X10	37.80	43.20	33.60
XY-MX4.2A-22A51	2X11	42.00	47.40	37.80
XY-MX4.2A-24A51	2X12	46.20	51.60	42.00


DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 4.2A 垂直式 WTB 插座	
X.:±0.50	±1°	CHK.	Jack	DWG NO. XY-MX4.2A-NA51	
X.X:±0.20		DRA.	Can	PROJ.  CUSTOMER DRAWING	
X.XX:±0.10		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A




2*2




2*3




2*4




2*5




2*6




2*7




2*8




2*9



2*10



2*11



2*12

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

X.:±0.50

±1°

X.X:±0.20

X.XX:±0.10

APR.

Alex

CHK.

Jack

DRA.

Can

厦门市辛译精密电子有限公司
Xiamen XinYi Xyeconn Electronics Co.,Ltd

TITLE:

4.2A 贴片式 WTB 封装

DWG NO.

XY-MX4.2A-NA51

PROJ.



CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/1

REV. A