







| 序号 | 品名                      | 材质                     |
|----|-------------------------|------------------------|
| ①  | 1.2 Pitch B型2代电<br>池座胶芯 | LCP UL94 V-0,<br>颜色:黑色 |
| ②  | 1.2 Pitch B型2代电<br>池座端子 | 铜合金/表面镀金               |
| ③  | 1.2 Pitch B型2代电<br>池座焊片 | 铜合金/表面镀金               |

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V AC, DC。
4. 耐电压: 500V AC/minute。
5. 接触电阻:  $\leq 20\text{m}\Omega$ 。
6. 绝缘电阻:  $\geq 100\text{M}\Omega$ 。
7. 额定电流: 1.5A AC, DC。



适用线路板(PCB LAYOUT)

| Part No            | CKT | A     | B     | C     | D     |
|--------------------|-----|-------|-------|-------|-------|
| XY-PE1.2-2PWB-B4A  | 2   | 4.20  | 1.20  | 2.65  | 3.64  |
| XY-PE1.2-3PWB-B4A  | 3   | 5.40  | 2.40  | 3.85  | 4.84  |
| XY-PE1.2-4PWB-B4A  | 4   | 6.60  | 3.60  | 5.05  | 6.04  |
| XY-PE1.2-5PWB-B4A  | 5   | 7.80  | 4.80  | 6.25  | 7.24  |
| XY-PE1.2-6PWB-B4A  | 6   | 9.00  | 6.00  | 7.45  | 8.44  |
| XY-PE1.2-7PWB-B4A  | 7   | 10.20 | 7.20  | 8.65  | 9.64  |
| XY-PE1.2-8PWB-B4A  | 8   | 11.40 | 8.40  | 9.85  | 10.84 |
| XY-PE1.2-9PWB-B4A  | 9   | 12.60 | 9.60  | 11.05 | 12.04 |
| XY-PE1.2-10PWB-B4A | 10  | 13.80 | 10.80 | 12.25 | 13.24 |
| XY-PE1.2-11PWB-B4A | 11  | 15.00 | 12.00 | 13.45 | 14.44 |
| XY-PE1.2-12PWB-B4A | 12  | 16.20 | 13.20 | 14.65 | 15.64 |

| DIMENSION IN mm                      |     | 厦门市辛译精密电子有限公司<br>Xiamen XinYi Xyconn Electronics Co.,Ltd |                                                                                                              |           |        |
|--------------------------------------|-----|----------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|-----------|--------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |     |                                                          |                                                                                                              |           |        |
| X.:±0.30                             | ±1° | APR. Alex                                                | TITLE: 1.20 Pitch B型2代电                                                                                      |           |        |
| X.X:±0.20                            |     | CHK. Jack                                                | DWG NO. XY-PE1.2-NA61-AU1                                                                                    |           |        |
| X.XX:±0.10                           |     | DRA. Can                                                 | PROJ.  CUSTOMER DRAWING |           |        |
|                                      |     | SIZE A4                                                  | SCALE 1:1                                                                                                    | SHEET 1/1 | REV. A |