

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED

备注:

1.材质:

1.1胶芯: LCP+30%G.F UL94V-0

1.2端子: C7025 : 镍底50U" MIN

接触区域镀金 (AU 1u")焊接区域镀金G/F

1.3外壳: SUS304, T=0.30mm: 表面镀镍30U" MIN

1.4中夹片: SUS301:

2.主要特性:

2.1额定电流: 5A

2.2接触阻抗: 40mΩ MAX (初始值)
50mΩ MAX (测试后)

2.3绝缘阻抗: 100MΩ MIN

2.4耐压测试: 100V AC R M S

2.5整体插入力:5-20N 整体插入力: 5-20N (耐久后)

整体拔出力: 8-20N 整体拔出力: 6-20N (耐久后)









2.6耐久: 10000次

2.7耐高温: SMT回流焊 (峰值260°±5°), 塑胶不能有起泡, 融胶等不良, 变色, 翘曲变形在公差范围以内。

2.8产品须做焊锡测试, 粘锡面积达到95%以上:

2.9盐雾测试: 24H MIN

3.0工作温度: -25°C ~ +80°C




RECOMMENDED P. C. B. LAYOUT (俯视图)

TOLERANCE UNSPECIFIED ±0.05mm

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

料号编码:



Part Number		Product Description				
WTT-03F16AD930CG37		TYPE-C 16PIN Vertical Connector Board, Model B, H=9.3MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.35 X.X ± 0.25 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)			
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang		 3rd Angle Projection			
Drawing Date	22/05/24					



WTT®

用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 2
--------------	-------------	------------------

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED

包装示意图:



- 备注:
1. 把上下载带送入载带机进行调整, 然后将产品按照指定的方式摆入下载带中, 开动卷带机进行卷装(每卷包500PCS)。
 2. 在卷装OK的每卷盘面的指定位置上贴上物料标签装入纸箱内; 每箱装10盘
 3. 纸箱用封箱带将其封好, 胶带要求工字型, 不可遮住标签;
 4. 如果客户对包装标签另有要求, 请按客户要求作业; 有未满足之零数箱需用缓冲材料填充;
 5. 上载带剥离力:0.2~1.2N. ;

包 装 信 息	
每盘产品数	500pcs
每箱卷盘数	10卷
每箱产品数	5000pcs
产品单重	依实际填写
每箱净重	依实际填写
每箱毛重	依实际填写

Part Number		Product Description				
WTT-03F16AD930CG37		TYPE-C 16PIN Vertical Connector Board, Model B, H=9.3MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.35 X.X ± 0.25 X.XX ± 0.15 X.XXX ± 0.10	Units: Metric (mm)  3rd Angle Projection	 COMPLIANT 2012 UL LLC UL94V-0	 RoHS COMPLIANT 2011/05/EU Deca-BDE	 REACH COMPLIANT 2011/05/EU SVHC
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24					



用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 2 or 2
--------------	-------------	------------------