









技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压: 100V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.

材料:

1. 塑胶: PA66 白色

PART NO	PIN	A	B	C	D
WAFER-ZH1.5-2PJK-KGW	2	1.50	3.40	4.50	2.30
WAFER-ZH1.5-3PJK-KGW	3	3.00	4.90	6.00	3.00
WAFER-ZH1.5-4PJK-KGW	4	4.50	6.40	7.50	3.00
WAFER-ZH1.5-5PJK-KGW	5	6.00	7.90	9.00	4.50
WAFER-ZH1.5-6PJK-KGW	6	7.50	9.40	10.50	6.00
WAFER-ZH1.5-7PJK-KGW	7	9.00	10.90	12.00	
WAFER-ZH1.5-8PJK-KGW	8	10.50	12.40	13.50	
WAFER-ZH1.5-9PJK-KGW	9	12.00	13.90	15.00	
WAFER-ZH1.5-10PJK-KGW	10	13.50	15.40	16.50	
WAFER-ZH1.5-11PJK-KGW	11	15.00	16.90	18.00	
WAFER-ZH1.5-12PJK-KGW	12	16.50	18.40	19.50	
WAFER-ZH1.5-13PJK-KGW	13	18.00	19.90	21.00	
WAFER-ZH1.5-14PJK-KGW	14	19.50	21.40	22.50	
WAFER-ZH1.5-15PJK-KGW	15	21.00	22.90	24.00	
WAFER-ZH1.5-16PJK-KGW	16	22.50	24.40	25.50	

SECTION A-A
SCALE 1:1

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: ZH1.5 WTB 公头带扣胶壳		
			PAR	WAFER-ZH1.5-NPJK-KGW	
			DWN	Lucas	
			CHKD	Ethan	
			APVD	Jacob	
DECIMALS:	ANGLES:		SCALE1:1	UNIT:MM	
X.:±0.50	±1°				
X.X:±0.20					
X.XX:±0.10		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A