






技术指标:


1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 100V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.

材料:

1. 塑胶: PA66 白色




PART NO	PIN	A	B	C
WAFER-ZH1.5-2PJK-BGW	2	1.50	3.40	4.5
WAFER-ZH1.5-3PJK-BGW	3	3.00	4.90	6.0
WAFER-ZH1.5-4PJK-BGW	4	4.50	6.40	7.5
WAFER-ZH1.5-5PJK-BGW	5	6.00	7.90	9.0
WAFER-ZH1.5-6PJK-BGW	6	7.50	9.40	10.5
WAFER-ZH1.5-7PJK-BGW	7	9.00	10.90	12.0
WAFER-ZH1.5-8PJK-BGW	8	10.50	12.40	13.5
WAFER-ZH1.5-9PJK-BGW	9	12.00	13.90	15.0
WAFER-ZH1.5-10PJK-BGW	10	13.50	15.40	16.5
WAFER-ZH1.5-11PJK-BGW	11	15.00	16.90	18.0
WAFER-ZH1.5-12PJK-BGW	12	16.50	18.40	19.5
WAFER-ZH1.5-13PJK-BGW	13	18.00	19.90	21.0
WAFER-ZH1.5-14PJK-BGW	14	19.50	21.40	22.5
WAFER-ZH1.5-15PJK-BGW	15	21.00	22.90	24.0
WAFER-ZH1.5-16PJK-BGW	16	22.50	24.40	25.5



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: ZH1.5 WTB公头胶壳		
DECIMALS:		PAR		
X.: ± 0.50		DWN		
X.X: ± 0.20		CHKD		
X.XX: ± 0.10		APVD		
		SCALE: 1:1		
		UNIT: MM		
		SIZE: A4		
		SHEET: 1F2		
		REV: A		

ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: ZH1.5 WTB公头胶壳
DECIMALS:	ANGLES:		PAR WAFER-ZH1.5-NPJK-BGW
X.:±0.50	±1°		DWN Lucas
X.X:±0.20			CHKD Ethan
X.XX:±0.10		CUSTOMER COPY	
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:2F2
			REV:A