

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED

备注:

1.材质:

1.1 胶芯: LCP+30%G.F UL94V-0

1.2 端子: 高导铜C7025, T=0.15mm;

1.3 外壳: SUS304, T=0.30mm;

1.4 中夹片: SUS301, T=0.15mm;

2.主要特性:

2.1额定电压: 20V

2.2额定电流: 5A

2.3接触阻抗: 40mΩ MAX(初始值)
50mΩ MAX(测试后)

2.4绝缘阻抗: 100MΩ MIN

2.5耐压测试: 100V AC R.M.S.

2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)

整体拔出力:8-20N 整体拔出力:6-20N (耐久后)

2.7耐久: 10000次



2.8耐高温: 建议1. 波峰焊 2. SMT回流焊 (峰值260°±5°),

塑胶不能有起泡, 融胶等不良, 变色, 翘曲变形在公差范围以内;

2.9产品须做焊锡测试, 粘锡面积达到95%以上;









3.0盐雾测试: 48H

3.1工作温度: -30℃~+85℃




PIN NUMBER	SIGNAL NAME
A1	GND
A4	VBUS
A5	CC1
A6	Dp1
A7	Dn1
A8	SBU1
A9	VBUS
A10	SSRXn2
A11	SSRXp2
A12	GND

PIN NUMBER	SIGNAL NAME
B12	GND
B9	VBUS
B8	SBU2
B7	Dn2
B6	Dp2
B5	CC2
B4	VBUS
B3	SSTXn2
B2	SSTXp2
B1	GND



RECOMMENDED P.C.B. LAYOUT (俯视图)
TOLERANCE UNSPECIFIED ±0.05mm

料号编码:




Part Number		Product Description		
WTT-04F16AD150CG66		TYPE-C 16PIN upright plug-in board without spring plate H15.0MM		
CUSTOMER DRAWING				
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm)	
CHECKED	Xiong fangyuan			
APPROVED	Huangshaohuang			
Drawing Date	22/05/24			


用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 1 or 2
--------------	-------------	------------------

REV.	ECR#	DESCRIPTION	DATE	DRAWN	CHECKED	APPROVED



包装示意图:



备注:

- 1.把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包300PCS),
- 2.在卷装OK的每卷盘面的指定位置上贴上物料标签装入纸箱内;每箱装10盘(3K/箱)
- 3.纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
- 4.如果客户对包装标签另有要求,请按客户要求作业;有未满足之零数箱需用缓冲材料填充;
- 5.上载带剥离力:0.2-1.2N.;

TABLE :

规格H	PCS/载带	K/箱
13.70	300PCS	3K
15.0		

Part Number		Product Description				
WTT-04F16AD150CG66		TYPE-C 16PIN upright plug-in board without spring plate H15.0MM				
CUSTOMER DRAWING						
DRAWN	Zhang Xincheng	Tolerances (Except as Noted) GENERAL TOLERANCE: X. ± 0.40 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm)			
CHECKED	Xiong fangyuan					
APPROVED	Huangshaohuang					
Drawing Date	22/05/24		 3rd Angle Projection			



用心连接世界

SCALE 1:1	SIZE: A4	SHEET: 2 or 2
--------------	-------------	------------------