






## 技术指标:


- 1.温度范围:  $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ .
- 2.额定电压: 100V AC,DC.
- 3.耐电压: 500V AC/minute.
- 4.接触电阻:  $\leq 20\text{m}\Omega$ .
- 5.绝缘电阻:  $\geq 500\text{M}\Omega$ .
- 6.额定电流: 1A AC,DC.

## 材料:

- 1.塑胶: PA66 白色



| PART NO           | PIN | A     | B     | C    |
|-------------------|-----|-------|-------|------|
| XY-ZH1.5-2A41-GW  | 2   | 1.50  | 3.40  | 4.5  |
| XY-ZH1.5-3A41-GW  | 3   | 3.00  | 4.90  | 6.0  |
| XY-ZH1.5-4A41-GW  | 4   | 4.50  | 6.40  | 7.5  |
| XY-ZH1.5-5A41-GW  | 5   | 6.00  | 7.90  | 9.0  |
| XY-ZH1.5-6A41-GW  | 6   | 7.50  | 9.40  | 10.5 |
| XY-ZH1.5-7A41-GW  | 7   | 9.00  | 10.90 | 12.0 |
| XY-ZH1.5-8A41-GW  | 8   | 10.50 | 12.40 | 13.5 |
| XY-ZH1.5-9A41-GW  | 9   | 12.00 | 13.90 | 15.0 |
| XY-ZH1.5-10A41-GW | 10  | 13.50 | 15.40 | 16.5 |
| XY-ZH1.5-11A41-GW | 11  | 15.00 | 16.90 | 18.0 |
| XY-ZH1.5-12A41-GW | 12  | 16.50 | 18.40 | 19.5 |
| XY-ZH1.5-13A41-GW | 13  | 18.00 | 19.90 | 21.0 |
| XY-ZH1.5-14A41-GW | 14  | 19.50 | 21.40 | 22.5 |
| XY-ZH1.5-15A41-GW | 15  | 21.00 | 22.90 | 24.0 |
| XY-ZH1.5-16A41-GW | 16  | 22.50 | 24.40 | 25.5 |



| DIMENSION IN mm                      |                 | 厦门市辛译精密电子有限公司<br>Xiamen XinYi Xyeconn Electronics Co.,Ltd |      |                          |                  |
|--------------------------------------|-----------------|-----------------------------------------------------------|------|--------------------------|------------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |                 |                                                           |      |                          |                  |
| X.: $\pm 0.50$                       | $\pm 1^{\circ}$ | APR.                                                      | Alex | TITLE: ZH1.5 WTB公头胶壳     |                  |
| X.X: $\pm 0.20$                      |                 | CHK.                                                      | Jack | DWG NO. XY-ZH1.5-NA41-GW |                  |
| X.XX: $\pm 0.10$                     |                 | DRA.                                                      | Can  | PROJ.                    | CUSTOMER DRAWING |
|                                      |                 | SIZE                                                      | A4   | SCALE                    | SHEET 1/2 REV.   |

