






RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4



序号	品名	材质
①	0.5 Pitch B型 单槽立式BTB公座嵌芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型 单槽立式BTB公座端子	铜合金/表面镀金
③	0.5 Pitch B型 单槽立式BTB公座焊片	铜合金/表面镀锡

Part No	CKT	A	B	C	D	E
LCK-BTG0526-10PDLYC-GO	2X5	2.00	3.10	4.60	5.52	4.10
LCK-BTG0526-12PDLYC-GO	2X6	2.50	3.60	5.10	6.02	4.60
LCK-BTG0526-14PDLYC-GO	2X7	3.00	4.10	5.60	6.52	5.10
LCK-BTG0526-16PDLYC-GO	2X8	3.50	4.60	6.10	7.02	5.60
LCK-BTG0526-18PDLYC-GO	2X9	4.00	5.10	6.60	7.52	6.10
LCK-BTG0526-20PDLYC-GO	2X10	4.50	5.60	7.10	8.02	6.60
LCK-BTG0526-22PDLYC-GO	2X11	5.00	6.10	7.60	8.52	7.10
LCK-BTG0526-24PDLYC-GO	2X12	5.50	6.60	8.10	9.02	7.60
LCK-BTG0526-26PDLYC-GO	2X13	6.00	7.10	8.60	9.52	8.10
LCK-BTG0526-28PDLYC-GO	2X14	6.50	7.60	9.10	10.02	8.60
LCK-BTG0526-30PDLYC-GO	2X15	7.00	8.10	9.60	10.52	9.10
LCK-BTG0526-32PDLYC-GO	2X16	7.50	8.60	10.10	11.02	9.60
LCK-BTG0526-34PDLYC-GO	2X17	8.00	9.10	10.60	11.52	10.10
LCK-BTG0526-36PDLYC-GO	2X18	8.50	9.60	11.10	12.02	10.60
LCK-BTG0526-38PDLYC-GO	2X19	9.00	10.10	11.60	12.52	11.10
LCK-BTG0526-40PDLYC-GO	2X20	9.50	10.60	12.10	13.02	11.60
LCK-BTG0526-44PDLYC-GO	2X22	10.50	11.60	13.10	14.02	12.60
LCK-BTG0526-50PDLYC-GO	2X25	12.00	13.10	14.60	15.52	14.10
LCK-BTG0526-60PDLYC-GO	2X30	14.50	15.60	17.10	18.02	16.60
LCK-BTG0526-70PDLYC-GO	2X35	17.00	18.10	19.60	20.52	19.10
LCK-BTG0526-80PDLYC-GO	2X40	19.50	20.60	22.10	23.02	21.60

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ±0.25		CHECKED		DATE	
X.x ±0.20		APPROVED		DATE	
X.xx ±0.15		PART NO: LCK-BTG0526-XXPDLYC-GO		TITLE: 0.5 Pitch B型单槽立式BTB公座焊片(单高2.6)	
ANGULAR ±3°		DRAWING NO: 102022802		REV: 04	SCALE: 1:1
				SIZE: A4	UNIT: mm
				SHEET: 1/1	