





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PART NO	PIN	A	B	C	D	E
C-ZH1.5-1-MEW2P62	2	1.50	4.82	3.66	4.50	3.00
C-ZH1.5-1-MEW3P62	3	3.00	6.32	5.16	6.00	3.00
C-ZH1.5-1-MEW4P62	4	4.50	7.82	6.66	7.50	4.50
C-ZH1.5-1-MEW5P62	5	6.00	7.90	8.16	9.00	6.00
C-ZH1.5-1-MEW6P62	6	7.50	9.40	9.66	10.50	7.50
C-ZH1.5-1-MEW7P62	7	9.00	10.90	11.16	12.00	9.00
C-ZH1.5-1-MEW8P62	8	10.50	12.40	12.66	13.50	10.50
C-ZH1.5-1-MEW9P62	9	12.00	13.90	14.16	15.00	12.00
C-ZH1.5-1-MEW10P62	10	13.50	15.40	15.66	16.50	13.50
C-ZH1.5-1-MEW11P62	11	15.00	16.90	17.16	18.00	15.00
C-ZH1.5-1-MEW12P62	12	16.50	18.40	18.66	19.50	16.50
C-ZH1.5-1-MEW13P62	13	18.00	19.90	20.16	21.00	18.00
C-ZH1.5-1-MEW14P62	14	19.50	21.40	21.66	22.50	19.50
C-ZH1.5-1-MEW15P62	15	21.00	22.90	23.16	24.00	21.00
C-ZH1.5-1-MEW16P62	16	22.50	24.40	24.66	25.50	22.50

技术指标:

- 1.温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压: 100V AC,DC.
- 3.耐电压: 500V AC/minute.
- 4.接触电阻: $\leq 20\text{m}\Omega$.
- 5.绝缘电阻: $\geq 500\text{M}\Omega$.
- 6.额定电流: 1A AC,DC.

材料:

- 1.塑胶: PA66 白色

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		C-ZH1.5-1-MEWNP62	ZH1.5 WTB 母座带扣胶壳		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---				
				SCALE N:A	SHEET 1/1