









RECOMMENDED P.C.B. PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

Note:

1. Material:

- 1.1 Housing: thermoplastic high temp.UL94V-0; Color: natural.
- 1.2 Latch: thermoplastic high temp.UL94V-0; Color: black.
- 1.3 Terminal: copper alloy.
- 1.4 Fitting Nail: copper alloy.

2. Finish:

- 2.1 Terminal:
Underplating: Au/matt Tin overall.
- 2.2 Fitting Nail:
Underplating: matt Tin overall.

3. Product must comply HF RoHS specification.

4. Product No:

- 5001-FPC 10 20 - ** R 1-00 -B
- Standby
- ALTERNATE
- PACKING:R:卷;T:管
- PIN
- HIGH:2.0
- PITCH:1.0
- 翻盖下接
- JME CONNECTOR SERIES

CKTS	DIM A	DIM B	DIM C
4	3.00	5.10	8.90
5	4.00	6.10	9.90
6	5.00	7.10	10.90
7	6.00	8.10	11.90
8	7.00	9.10	12.90
9	8.00	10.10	13.90
10	9.00	11.10	14.90
11	10.00	12.10	15.90
12	11.00	13.10	16.90
13	12.00	14.10	17.90
14	13.00	15.10	18.90
15	14.00	16.10	19.90
16	15.00	17.10	20.90
17	16.00	18.10	21.90
18	17.00	19.10	22.90
19	18.00	20.10	23.90
20	19.00	21.10	24.90
21	20.00	22.10	25.90
22	21.00	23.10	26.90
23	22.00	24.10	27.90
24	23.00	25.10	28.90
25	24.00	26.10	29.90
26	25.00	27.10	30.90
27	26.00	28.10	31.90
28	27.00	29.10	32.90
29	28.00	30.10	33.90
30	29.00	31.10	34.90

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size (图幅): A4
0.0 ±0.15 0° ±5°	Unit (单位): MM
0.00 ±0.10 0° ±3°	Scale (比例): 1:1
0.000 ±0.05 0° ±1°	Project View (投影视角)
1 OF 1	Page (页数): 1 OF 1
Rev (版本): A	Rev (版本): A

深圳市文章济美科技有限公司

Shenzhen WenZhangJiMei technology co., LTD

Product Name (产品名称):
1.0Pitch H=2.0 FPC Easy-on R/A Type1 SMT CONN

Product No (产品料号):
5001-FPC1020-**R1-00-B

Designer (设计):
Allan 03/23'11

Checked (审核):

Approved (核准):

Rev 版本	初版发行 变更内容	2011/03/23 日期	Allan Revisor 制/修订人
-----------	--------------	------------------	---------------------------