


ROHS+HF Complied


FOR PEGATRON

PART NO.	POS.	A	B	C	D	E	F	G	H	I	J
ALC04-S20	20	9.50	16.25	11.30	14.30	18.20	15.90	10.60	10.90	11.66	12.60
ALC04-S30	30	14.50	21.25	16.30	19.30	23.20	20.90	15.60	15.90	16.66	17.60
ALC04-S40	40	19.50	26.25	21.30	24.30	28.20	25.90	20.60	20.90	21.66	22.60
ALC04-S50	50	24.50	31.25	26.30	29.30	33.20	30.90	25.60	25.90	26.66	27.60












SECTION A–A







RECOMMEND P.C.B BOARD LAYOUT

NO TRACE,NO TEST POINT,NO VIA HOLE,NO GROUND AREA (PLUG WITH PULL BAR USE AREA)

NO TRACE,NO TEST POINT,NO VIA HOLE,NO GROUND AREA (RECEPTACLE & PULL USE AREA)

NOTES:

1. UNLESS OTHERWISE SPECIFIED,ALL TOLERANCES FOLLOW DRAWING COMMON STANDARD.
2. PART NO:ALC04-S**E * A -**

PIN NO.
- 20:20 POSITION
- 30:30 POSITION
- 40:40 POSITION
- 50:50 POSITION

PLATING:
- 1:CONTACT AREA: GOLD FLASH / SOLDER AREA: GOLD FLASH
- 3:CONTACT AREA: 3u" GOLD / SOLDER AREA: GOLD FLASH
- 4:CONTACT AREA: 5u" GOLD / SOLDER AREA: GOLD FLASH
- 5:CONTACT AREA: 10u" GOLD / SOLDER AREA: GOLD FLASH
- Q:CONTACT AREA: 15u" GOLD / SOLDER AREA: GOLD FLASH

-**
- 00:PH 8/WIDTH 44(正向)40/50P
- 00:PH 8/WIDTH 32(正向)30P
- 01:PH 8/WIDTH 44(正向)30P
- 01:PH 12/WIDTH 44(正向)40P
- 02:PH 12/WIDTH 44(正向)30P
- 01:PH 8/WIDTH 44(反向)50P
- 02:PH 8/WIDTH 44(反向)40P
- 03:PH 8/WIDTH 32(反向)30P
- 03:PH 12/WIDTH 44(反向)40P
- 04:PH 8/WIDTH 44(反向)30P
- 05:PH 12/WIDTH 44(反向)30P
- 00:PH 8/WIDTH 24(正向)20P
- 01:PH 8/WIDTH 24(反向)20P

NO.	PART NAME	QTY.	MATERIAL	REMARK
③	SHELL	1	COPPER ALLOY(C5210) t=0.12	SOLDER AREA PLATED GOLD FLASH, Ni 50u" Min OVER ALL.
②	TERMINAL	20/30/40/50	COPPER ALLOY(C5210) t=0.12	CONTACT PLATING SEE P/N AND SOLD TAIL,Ni 50u" Min OVER ALL.
①	HOUSING	1	GLASS FILLED LCP E473i UL94V-0	BLACK

CUSTOMER DRAWING

浙江创都电子科技有限公司

Tolerance Unspecified (未注公差)
0.0 ±0.25 0°. ±5°
0.00 ±0.15 0°.0 ±3°
0.000 ±0.10 0°.00 ±1°

Size(图幅): A4
Unit(单位): MM
Scale(比例): 1 : 1
Page(页数): 1 OF 1
Rev(版本): 1.0

Project View (投影视角)

PART NO： CAX-LXALC04LVDS-S40BA

料号编码 ALC04-S**E*A-**

Designer(设计):
Checked(审核):
Approved(核准):

Rev 版本	Change Description 变更内容	Date 日期	Revisor 制/修订人
1.0	初版发行	2020/12/30	