

ROHS+HF Complied


FOR PEGATRON


PART NO.	POS.	A	B	C	D	E	F	G	H	I	J
ALC04-S20	20	9.50	16.25	11.30	14.30	18.20	15.90	10.60	10.90	11.66	12.60
ALC04-S30	30	14.50	21.25	16.30	19.30	23.20	20.90	15.60	15.90	16.66	17.60
ALC04-S40	40	19.50	26.25	21.30	24.30	28.20	25.90	20.60	20.90	21.66	22.60
ALC04-S50	50	24.50	31.25	26.30	29.30	33.20	30.90	25.60	25.90	26.66	27.60







MATING CONDITION(S=2:1)






SECTION A–A







RECOMMEND P.C.B BOARD LAYOUT

NO TRACE,NO TEST POINT,NO VIA HOLE,NO GROUND AREA (PLUG WITH PULL BAR USE AREA)

NO TRACE,NO TEST POINT,NO VIA HOLE,NO GROUND AREA (RECEPTACLE & PULL USE AREA)

NOTES:

1. UNLESS OTHERWISE SPECIFIED,ALL TOLERANCES FOLLOW DRAWING COMMON STANDARD.
2. PART NO:ALC04-S**E * A -**

PIN NO.
- 20:20 POSITION
- 30:30 POSITION
- 40:40 POSITION
- 50:50 POSITION

PLATING:
- 1:CONTACT AREA: GOLD FLASH
  SOLDER AREA: GOLD FLASH
- 3:CONTACT AREA: 3u" GOLD
  SOLDER AREA: GOLD FLASH
- 4:CONTACT AREA: 5u" GOLD
  SOLDER AREA: GOLD FLASH
- 5:CONTACT AREA: 10u" GOLD
  SOLDER AREA: GOLD FLASH
- Q:CONTACT AREA: 15u" GOLD
  SOLDER AREA: GOLD FLASH

-**
- 00:PH 8/WIDTH 44(正向)40/50P
- 00:PH 8/WIDTH 32(正向)30P
- 01:PH 8/WIDTH 44(正向)30P
- 01:PH 12/WIDTH 44(正向)40P
- 02:PH 12/WIDTH 44(正向)30P
- 01:PH 8/WIDTH 44(反向)50P
- 02:PH 8/WIDTH 44(反向)40P
- 03:PH 8/WIDTH 32(反向)30P
- 03:PH 12/WIDTH 44(反向)40P
- 04:PH 8/WIDTH 44(反向)30P
- 05:PH 12/WIDTH 44(反向)30P
- 00:PH 8/WIDTH 24(正向)20P
- 01:PH 8/WIDTH 24(反向)20P

NO.	PART NAME	QTY.	MATERIAL	REMARK
③	SHELL	1	COPPER ALLOY(C5210) t=0.12	SOLDER AREA PLATED GOLD FLASH, Ni 50u" Min OVER ALL.
②	TERMINAL	20/30/40/50	COPPER ALLOY(C5210) t=0.12	CONTACT PLATING SEE P/N AND SOLD TAIL,Ni 50u" Min OVER ALL.
①	HOUSING	1	GLASS FILLED LCP E473i UL94V-0	BLACK

Rev 版本	Change Description 变更内容	Date 日期	Revisor 制/修订人
1.0	初版发行	2020/12/30	

浙江创都电子科技有限公司

Tolerance Unspecified (未注公差)
0.0 ±0.25 0°. ±5°
0.00 ±0.15 0°.0 ±3°
0.000 ±0.10 0°.00 ±1°

Size(图幅): A4
Unit(单位): MM
Scale(比例): 1 : 1
Page(页数): 1 OF 1
Rev(版本): 1.0
Project View (投影视角)

PART NO： CAX-LXALC04LVDS-S30BA

料号编码 ALC04-S**E*A-**

Designer(设计): Andy
Checked(审核):
Approved(核准):