
RoHS Compliant


Process Capable

IPX7

1m/30min

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B	---	UPGRADER DRAWINGS		







组装示意图


开孔尺寸参考


组装外壳时需要打环保润滑油


Note:
1.Material:
1.1 Housing: LCP
1.2 Contact:C7025,t=0.20mm
1.3 Shell: SUS316
2.ELECTRICAL:
2-1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 1.25A
PARALLELED FOR A TOTAL OF 5A;
2-2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2-3:DIEELECTRIC WITHSTANDING VOLTAGE:
100V AC MIN;
3:MECHANICAL CHARACTERISTICS:
3-1:MATING FORCE:5~20N
3-2:UNMATING FORCE:8~20N(INITIAL),
6~20N(AFTER 10000 CYCLES)
3-3:FREQUENCE: 200±50 CYCLES /HOUR,
10000 CYCLES
3-4:OPERATING TEMPERATURE :-40°~80°.













RECOMMENDED P.C.B. LAYOUT

TOLERANCE UNSPECIFIED ±0.05mm



AFTER MATING

Suggested adsorption size



Added suction cover view

X. ±0.50	X.° ± 2°	UNITS	mm
.X ±0.30	.X° ± 1°	MAT'L	
.XX ±0.20	.XX° ± 0.5°		
.XXX ± 0.10		FINISH	
		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

Guangdong Chuangyue Technology Co.,Ltd

TITLE:

TYPE-C 16PIN直立式防水母座双筋位6.68 外壳粉末冶金

APPD:

CHKD:

DR:


DWG NO.:

TYPE-C-16P-H6.68SMT-00153


SCALE	SHEET	REV.
1/1	1/2	B

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B	---	UPGRADER DRAWINGS		




① 产品入载带示意图




② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	500	5500

包装说明：

1. 将检验好的成品；对插口朝前放入载带；每卷装500PCS产品；
2. 将包装好的产品；每盘必须贴上内标签；
3. 将贴好内标签的产品每11盘叠；
4. 装好后并封好纸箱及贴好相关标签；
   （产品包装的标签，如客户有要求，请按客户要求包装出货）
5. 载带前面留17PCS空格，后面留17PCS空格

X. ±0.50	X.° ± 2°	UNITS	mm
.X ±0.30	.X° ± 1°	MAT'L	
.XX ±0.20	.XX° ± 0.5°	FINISH	
.XXX ± 0.10		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE: TYPE-C 16PIN直立式防水母座双筋位6.68 外壳粉末冶金

APPD:
CHKD:
DR:

DWG NO.: TYPE-C-16P-H6.68SMT-00153

SCALE	SHEET	REV.
1/1	2/2	B