RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	DRAWINGS UPGRADE	ZXM	2026.01.21

NOTES:

特性：Specifications

电器 Electrical:

电流:3A Max.

电压：30V Max.

接触阻抗：初始最大不超过40mΩMax.,测试后变化值不超过10mΩ Max.

耐电压：AC200V 60S/MIN.,0.5mA Max:DC500V,60S/MIN.,100Ω Max.

绝缘阻抗：100M ohms MIN.

材料：Matorial:

主体：LCP料黑色耐高温塑胶

护套：LCP料黑色耐高温塑胶

端子：C5191磷铜 T=0.15MM.

外壳：不锈钢304 T=0.15MM.

卡勾；不锈钢301 T=0.30MM.

电镀规格：


端子：半金锡，接触点镀金1u”，焊脚处镀锡40-80u”.


外壳：镀镍30u”MIN.


卡钩：整体镀镍30u”MIN.焊脚镀锡50u”MIN.


环保要求：ROHS,REACH标准.


包装方式：依客户需求（建议使用REEL包装）














RECOMMENDED P.C.B. LAYOUT

TOLERANCE UNSPECIFIED ±0.05mm

PIN ASSIGNMENTS:

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND			VBUS	SBU1	D-	D+	CC	VBUS	TX1-	TX1+	GND


B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
									RX1-	RX1+	

X. ±0.50	X.° ± 2°	UNITS	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	mm	Guangdong Chuangyue Technology Co.,Ltd
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: CM 12PIN__卡勾带插脚(铆压款)
.XXX ±0.10		FINISH	APPD: CZN / PART NO.: TYPE-CM-12P-H11.5-00118
		Q'TY	CHKD: CZJ / SCALE 1/1 / SHEET 1/2 / REV. C
			DR: ZXM


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPROOUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	DRAWINGS UPGRADE	ZXM	2026.01.21




① 产品入载带示意图




② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装1200PCS产品;
2. 将包装好的产品;每盘必须贴上内标签;
3. 将贴好内标签的产品每11盘叠;
4. 装好后并封好纸箱及贴好相关标签;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
5. 载带前面留15PCS空格，后面留15PCS空格

	REEL	CARTON
CONNECTOR (PCS)	1200	13200

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPROOUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE: CM 12PIN__卡勾带插脚(铆压款)

APPD: CZN

CHKD: CZJ

DR: ZXM

PART NO.: TYPE-CM-12P-H11.5-00118

SCALE	SHEET	REV.
1/1	2/2	C