


Kinghelm®

REV.	ECN NO OR DESCRIPTION	REVISED	DATE







NOTES:


MATERIAL:
CAGE: COPPER ALLOY 30u" MIN NI-PLATED,THICKNESS 0.25 MM
CONNECTOR:
PLASTIC HOUSING: HIGH TEMPERATURE LCP, UL94 V-0.
SPRING: STAINLESS STEEL, THICKNESS 0.20mm
CONTACTS: PHOSPHOR BRONZE, THICKNESS 0.20mm
PLATING: 15μ" MIN. GOLD ON MATING AREA,
150μ" MIN. MATE TIN ON SOLDER TAILS.
PACKAGING: TRAY PACKAGING.
OPERATING TEMPERATURE: -40°C TO +85°C
STORAGE TEMPERATURE: -55°C TO +105°C

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRONIC CO.,LTD.
www.kinghelm.com.cn 0755-28190160


THIRD ANGLE PROJECTION	TITLE		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	PART NO: KH-SFP-K200-4105R	DRN BY: TONY	DATE: 12-10-08
DECIMALS: X±0.20 X.X±0.15 X.XX±0.10 ANGLES: X.°±0.2° X.X°±0.1°	Product: PCB JACK RJ45 RJ11 USB CONNECTOR SFP CONNECTOR TRANSFORMER	APPD BY: JIM	SHEET NO. 1 OF 4
DIMENSIONS: mm		DWG NO: SFP+ K20003	REV: A10

文件编号：RD-23-03-A


REV.	ECN NO OR DESCRIPTION	REVISED	DATE



CIRCUIT NUMBERING
COMPONENT SIDE OF BOARD



DETAIL A
CIRCUIT NUMBERING
AND LIGHTPIPE INDENTIRCATION



RECOMMENDED PCB LAYOUT – COMPONENT SIDE
RECOMMENDED PCB THICKNESS : 2.36MM(.093 INCH)
(MINIMUM PCB THICKNESS : 1.57)

THE ENTIRE AREA OF THE CONNECTOR FOOTPRINT
TO BE CONSIDERED THE KEEP OUT AREA FOR COMPONENTS
THIS AREA IS INDICATED BY THE DASHED LINE


深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRONIC CO.,LTD.
www.kinghelm.com.cn 0755-28190160

THIRD ANGLE PROJECTION	TITLE		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	PART NO: KH-SFP-K200-4105R	DRN BY: TONY	DATE: 12-10-08
DECIMALS: X±0.20 X.X±0.15 X.XX±0.10 ANGLES: X.°±0.2° X.X°±0.1°	Product: PCB JACK RJ45 RJ11 USB CONNECTOR SFP CONNECTOR TRANSFORMER	APPD BY: JIM	SHEET NO. 2 OF 4
DIMENSIONS: mm		DWG NO: SFP+ K20003	REV: A10


文件编号：RD-23-03-A

Kinghelm®

REV.	ECN NO OR DESCRIPTION	REVISED	DATE



DETAIL–KEEPOUT ZONES



TERMINAL TAIL PATTERN

THE HATCHED AREA IN THIS VIEW INDICATES ZONES THAT ARE OCCUPIED BY THE PLASTIC HOUSING THAT SEATS AGAINST THE PCB AND BY THE VERTICAL METAL CAGE WALL THAT STOPS JUST SHORT OF THE PCB


深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRONIC CO.,LTD.
www.kinghelm.com.cn 0755-28190160

THIRD ANGLE PROJECTION	TITLE		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	PART NO: KH-SFP-K200-4105R	DRN BY: TONY	DATE: 12-10-08
DECIMALS: X±0.20 X.X±0.15 X.XX±0.10 ANGLES: X.°±0.2° X.X°±0.1°	Product: PCB JACK RJ45 RJ11 USB CONNECTOR SFP CONNECTOR TRANSFORMER	APPD BY: JIM	SHEET NO. 3 OF 4
DIMENSIONS: mm		DWG NO: SFP+ K20003	REV: A10


文件编号：RD-23-03-A

Kinghelm®

REV.	ECN NO OR DESCRIPTION	REVISED	DATE



BEZEL CUT-OUT CENTER SPACING DETAIL



SECTION Z-Z

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRONIC CO.,LTD.
www.kinghelm.com.cn 0755-28190160

THIRD ANGLE PROJECTION	TITLE		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	PART NO: KH-SFP-K200-4105R	DRN BY: TONY	DATE: 12-10-08
DECIMALS: X±0.20 X.X±0.15 X.XX±0.10 ANGLES: X.°±0.2° X.X°±0.1°	Product: PCB JACK RJ45 RJ11 USB CONNECTOR SFP CONNECTOR TRANSFORMER	APPD BY: JIM	SHEET NO. 4 OF 4
DIMENSIONS: mm		DWG NO: SFP+ K20003	REV: A10

文件编号：RD-23-03-A