

3EJT1F

✓ ACTIVE

Corcom | Corcom EJT


TE Internal #: 4-1609157-0

Multi-Function Inlet Filters, Power Line, Vertical, 3A Current Rating, .250" FASTON Output, Operating Voltage 250 VAC, Filtered, Corcom EJT

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > IEC Filtered Inlets, Corcom EJT Series



Filter Type: **Power Line**
Product Orientation: **Vertical**
Leakage Current (Max) (120VAC, 60Hz): **250 μ A**
Current Rating: **3 A**
Output Termination Type: **.250" FASTON**

[All IEC Filtered Inlets, Corcom EJT Series \(22\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Current Rating	3 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Vertical
---------------------	----------

Mechanical Attachment





Panel Mount Feature Type	Extended Flange
--------------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | Corcom EJT




Multi-Function Inlet Filters(22)

Customers Also Bought



TE Part #5747024-3
RFI GASKET, SIZE 1, PLATED



TE Part #350763-4
09P UMNL HDR ASSY PC



TE Part #640467-1
05P UMNL HDR ASSY



TE Part #745508-3
FERRULE SPLIT RING, HD



TE Part #350762-4
06P UMNL HDR ASSY PC




TE Part #350764-4
12P UMNL HDR ASSY PC



TE Part #350761-4
04P UMNL HDR ASSY PC



TE Part #1-770834-0
MINI UMNL SOK AU LF



TE Part #5747025-3
RFI GASKET, SIZE 2, PLATED



TE Part #2-2176337-2
CRGQ 0402 560R 1%

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_4-1609157-0_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1609157-0_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_4-1609157-0_B1.2d_dxf.zip

3EJT1F

Multi-Function Inlet Filters, Power Line, Vertical, 3A Current Rating, .250" FASTON Output, Operating Voltage 250 VAC, Filtered, Corcom EJT



English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
1654001_CORCOM_PRODUCT_GUIDE

English

Corcom EJT Flanged Inlet Filter

English

Corcom Combined Selector Charts

English