



SMA Female Field Replaceable Connector 2 Hole Flange Mount 0.018 inch Pin, .400 inch Hole Spacing with Metal Contact Ring

RF Connectors
Technical Data Sheet

PE45581

Configuration

- SMA Female Connector
- Straight Body Geometry

Features

- Max. Operating Frequency 27 GHz
- Excellent VSWR of 1.2:1

Applications

- General Purpose Test
- Rack and Panel Mount Applications

- Connector Interface Types: 0.018 inch Pin
- 2 Hole Flange
- Gold Plated Beryllium Copper Contact
- Metal Contact Ring
- Used in Product Requiring Hermetic Seals
- Allows for Replacement of Damaged Connectors

Description

Pasternack's PE45581 SMA female 2 hole flange mount field replaceable connector is part of our full line of RF components available for same-day shipping. Our SMA female connector operates up to a maximum frequency of 27 GHz and offers excellent VSWR of 1.2:1. This SMA 2 hole flange connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. This field replaceable connector is easy to install or replace in the field.

Our SMA female 2 hole flange connector PE45581 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		27	GHz
VSWR			1.2:1	

Mechanical Specifications

Size Length Width/Dia. Height

Weight
Mating Cycles

0.372 in [9.45 mm] 0.25 in [6.35 mm] 0.55 in [13.97 mm]

0.004 lbs [1.81 g]

500 Cycles

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female Field Replaceable Connector 2 Hole Flange Mount 0.018 inch Pin, .400 inch Hole Spacing with Metal Contact Ring PE45581

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





SMA Female Field Replaceable Connector 2 Hole Flange Mount 0.018 inch Pin, .400 inch Hole Spacing with Metal Contact Ring

RF Connectors Technical Data Sheet

PE45581

Material Specifications

Description	Material	Plating	
Contact	Beryllium Copper	Gold	
Insulation	PTFE		
Outer Conductor	Passivated Stainless Steel		
Body	Passivated Stainless Steel		

Environmental Specifications

Temperature

Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

SMA Female Field Replaceable Connector 2 Hole Flange Mount 0.018 inch Pin, .400 inch Hole Spacing with Metal Contact Ring from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female Field Replaceable Connector 2 Hole Flange Mount 0.018 inch Pin, .400 inch Hole Spacing with Metal Contact Ring PE45581

URL: https://www.pasternack.com/sma-female-0.018-pin-connector-pe45581-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE45581 CAD Drawing

SMA Female Field Replaceable Connector 2 Hole Flange Mount 0.018 inch Pin, .400 inch Hole Spacing with Metal Contact Ring

