### JRC

## DUAL OPERATIONAL AMPLIFIER


#### GENERAL DESCRIPTION


NJM4580 is the dual operational amplifier, specially designed for improving the tone control, which is most suitable for the audio application.

Featuring noiseless, higher gain bandwidth, high output current and low distortion ratio, and it is most suitable not only for acoustic electronic parts of audio pre-amp and active filter, but also for the industrial measurement tools. It is also suitable for the head phone amp at higher output current, and further more, it can be applied for the handy type set operational amplifier of genenal purpose in application of low voltage single supply type which is properly biased of the input low voltage source.

- FEATURES
- Operating Voltage
- Low Input Noise Voltage
- Wide Gain Bandwidth Product
- Low Distortion
- Slew Rate
- Package Outline
- Bipolar Technology

(±2V~±18V) (0.8 µVrms typ.) (15MHz typ.) (0.0005% typ.) (5V/ µs typ.) DIP8, SIP8, EMP8, SSOP8, DMP8 PACKAGE OUTLINE








NJM4580V

#### PIN CONFIGURATION

PIN FUNCTION 1. A OUTPUT A -INPUT 2. 3. A + INPUT 4. V 5. B +INPUT 2 1 6 6. B -INPUT 7. BOUTPUT NJM4580L 8. v NJM4580D, NJM4580E NJM4580M NJM4580V

**EQUIVALENT CIRCUIT** (1/2 Shown)



4-221

ABSOLUTE MAXIMUM RATINGS			(Ta=25℃)
PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V*/V~	±18	v
Input Voltage	Vic	±15 (note)	v
Differential Input Voltage	Vid	±30 (note)	v
Output Current	Io	±50	mA
Power Dissipation		(DIP8) 800	mW
		(SIP8) 800	mW
	PD	(DMP8) 300	mW
		(EMP8) 300	mW
		(SSOP8) 250	mW
Operating Temperature Range	Topr	-40~+85	°C
Storage Temperature Range	Tstg	-40~+125	C


#### ELECTRICAL CHARACTERISTICS

UNIT SYMBOL MAX. PARAMETER TEST CONDITION MIN. TYP. 0.5 Input Offset Voltage Vio  $R_{S} \leq 10 k \Omega$ 3 mV----Input Offset Current Ιıο \_\_\_ 5 200 nΑ Input Bias Current \_\_\_\_ 100 500 nΑ  $\mathbf{I}_{\mathrm{B}}$ Large Signal Voltage Gain Αv  $R_L \ge 2k\Omega, V_O = \pm 10V$ 90 110 dB Output Voltage Swing Vом  $R_L \ge 2k\Omega$  $\pm 12$ ±13.5 ٧ Input Common Mode Voltage Range  $V_{ICM}$ ±12  $\pm 13.5$ ٧ CMR  $R_{S} \leq 10 k \Omega$ 80 110 dB Common Mode Rejection Ratio Supply Voltage Rejection Ratio SVR  $R_{S} \leq 10 k \Omega$ 80 110 dB  $\mathsf{I}_{\mathsf{C}\mathsf{C}}$ 6 9 mΑ Operating Current Slew Rate SR  $R_L \geqq 2k\Omega$ 5 V/µs \_\_\_\_ Gain Bandwidth Product GB f = 10 Hz15 MHz -----THD  $A_V = 20 dB, V_O = 5V, R_L = 2k\Omega, f = 1kHz$ \_ % Total Harmonic Distortion 0.0005 Input Noise Voltage  $V_{\rm NI}$ RIAA  $R_s = 2.2k\Omega$ , 30kHzLPF \_\_\_\_ 0.8  $\mu V_{rms}$ 


 $(Ta=25^{\circ}C, V^{+}/V^{-}=\pm 15V)$ 

-New Japan Radio Co.,Ltd.-


#### TYPICAL CHARACTERISTICS




Output Voltage Swing vs. Output Current




**Operating Current vs. Temperature** 



Maximum Output Voltage Swing vs. Frquency  $(V^+/V^- = \pm 15V, R_1 = 2 k\Omega, Ta = 25^{\circ}C)$ 30 25 Voltage Swing 20 15 10 VOPP (V) 5 0 1 k 10k 100k 1M Frequency f (Hz)






-New Japan Radio Co.,Ltd.

-4-223

# NJM4580



TYPICAL CHARACTERISTICS

**MEMO** 

[CAUTION] The specifications on this databook are only given for information , without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.