


### **Adjustable LED Driver**

**TLE 4242 G** 

### **Features**

- Adjustable constant current up to 500 mA (±5%)
- Wide input voltage range up to 42 V
- Low drop voltage
- Open load detection
- Overtemperature protection
- Short circuit proof
- Reverse polarity proof
- Wide temperature range: -40 °C to 150 °C



### **Functional Description**

The TLE 4242 G is an integrated adjustable constant current source driving loads up to 500 mA. The output current level can be adjusted via an external resistor. The IC is designed to supply high power LEDs (e.g. Osram Dragon LA W57B) under the severe conditions of automotive applications resulting in constant brightness and extended LED lifetime. It is provided in the surface mounted P-TO263-7-1 package. Protection circuits prevent damage to the device in case of overload, short circuit, reverse polarity and overheat. The connected LEDs are protected against reverse polarity as well as excess voltages up to 45 V.

The integrated PWM input of the TLE 4242 G permits LED brightness regulation by pulse width modulation. Due to the high input impedance of the PWM input the LED driver can be operated as a protected high side switch.

Туре	Ordering Code	Package
TLE 4242 G	Q67006-A9674	P-TO263-7-1

Data Sheet 1 Rev. 1.0, 2004-01-01



### **Circuit Description**




Figure 1 Block Diagram

An external shunt resistor in the ground path of the connected LEDs is used to sense the LED current. A regulation loop helds the voltage drop at the shunt resistor on a constant level of typ. 177 mV. Selecting the shunt resistance permits to adjust the appropriate constant current level. The typ. output current calculates

$$I_{\rm Q,\,typ} = \frac{V_{\rm REF}}{R_{\rm RFF}} \tag{1}$$

where  $V_{\rm REF}$  is the reference voltage with a typical level of 177 mV (see Page 10). The equation applies in a range of 0.39  $\Omega \le R_{\rm BFF} \le$  1.8  $\Omega$ .

The output current is shown as a function of the reference resistance on Page 10. With the PWM input the LED brightness can be regulated via duty cycle. Also PWM = L sets the TLE 4242 in sleep mode resulting in a very low current consumption of << 1  $\mu$ A typ. Due to the high impedance of the PWM input (see "PWM Pin Input Current versus PWM Voltage" on Page 11) the PWM pin can thus also be used as an enable input.






Figure 2 Pin Configuration (top view)

Table 1 Pin Definitions and Functions

Pin No.	Symbol	Function
1	I	Input; block to GND directly at the IC with a 100 nF ceramic capacitor.
2	PWM	Pulse Width Modulation Input; if not needed connect to I
3	ST	<b>Status Output</b> ; open collector output, connect to external pull-up resistor ( $R_{\text{pull-up}} \ge 4.7 \text{ k}\Omega$ ).
4	GND	Ground
5	REF	Reference Input; connect to shunt resistor.
6	D	Status Delay; connect to GND via an optional capacitor to set status reaction delay. Leave open if no ST delay is needed.
7	Q	Output

Data Sheet 3 Rev. 1.0, 2004-01-01



### **Application Information**




Figure 3 Application Circuit

**Figure 3** shows a typical application with the TLE 4242 G LED driver. The 3 LEDs are driven with an adequate supply current adjusted by the resistor  $R_{\rm REF}$ . Thus brightness variations due to forward voltage spread of the LEDs are prevented. The luminosity spread arising from the LED production process can be compensated via software by an appropriate duty cycle applied to the PWM pin. Hence selection of the LEDs to forward voltage as well as to luminosity classes can be spared. The minimum supply voltage calculates as the sum of the LED forward voltages, the TLE 4242 G drop voltage (max. 0.7 V at a LED current of 300 mA) and the max. voltage drop at the shunt resistor  $R_{\rm REF}$  of max. 185 mV.

The status output of the LED driver (ST) detects an open load condition enabling to supervise correct LED function. A LED failure is detected if the voltage drop at the shunt resistor  $R_{\rm REF}$  falls below typ. 25 mV. In this case the status output pin ST is set low after a delay time adjustable via an optional capacitor connected to the pin D.

Data Sheet 4 Rev. 1.0, 2004-01-01



The functionality of the ST and PWM as well as their timings are shown in **Figure 4**. The Status delay can be adjusted via the capacitor connected to the timing Pin D. The delay time scales in linear way with the capacitance  $C_D$ :

$$t_{\text{STHL,typ}} = \frac{C_{\text{D}}}{47 \text{ nF}} \times 10 \text{ ms}$$
  $t_{\text{STLH,typ}} = \frac{C_{\text{D}}}{47 \text{ nF}} \times 10 \text{ }\mu\text{s}$  (2)




Figure 4 Function and Timing Diagram

Data Sheet 5 Rev. 1.0, 2004-01-01



 Table 2
 Absolute Maximum Ratings

-40 °C <  $T_{\rm i}$  < 150 °C

Parameter	Symbol	Limit	t Values	Unit	Remarks
		Min.	Max.		
Input		•		1	
Voltage	$V_{I}$	-42	45	V	_
Current	$I_{I}$	_	_	mA	internally limited
Output				1	•
Voltage	$V_{Q}$	-1	40	V	_
Current	$I_{Q}$	_	_	mA	internally limited
Status Output				1	•
Voltage	$V_{ST}$	-0.3	40	V	_
Current	$I_{ST}$	-5	5	mA	_
Status Delay			•	1	
Voltage	$V_{D}$	-0.3	7	V	_
Reference Input				1	•
Voltage	$V_{REF}$	-1	16	V	_
Current	$I_{REF}$	-2	2	mA	_
Pulse Width Modulation	n Input				
Voltage	$V_{PWM}$	-40	40	V	_
Current	_	-1	1	mA	_
Temperatures				1	•
Junction temperature	$T_{\rm j}$	-40	150	°C	_
Storage temperature	$T_{stg}$	-50	150	°C	_
Thermal Resistances	·	•		•	•
Junction ambient	$R_{\rm thja}$	_	78	K/W	Footprint only <sup>1)</sup>
		_	52	K/W	300mm <sup>2</sup> heat sink area
		_	39	K/W	600mm <sup>2</sup> heat sink area
Junction case	$R_{ m thjc}$	1-	3	K/W	_

<sup>1)</sup> Worst case regarding peak temperature; mounted on PCB FR4,  $80 \times 80 \times 1.5$  mm<sup>3</sup>, 35  $\mu$ m Cu.

Note: Maximum ratings are absolute ratings; exceeding any one of these values may cause irreversible damage to the integrated circuit.

Data Sheet 6 Rev. 1.0, 2004-01-01



Table 3 Operating Range

Parameter	Symbol	Limit	Values	Unit	Remarks
		Min.	Max.		
Input voltage	$V_{I}$	4.5	42	V	_
Status output voltage	$V_{ST}$	-	16	V	_
Status Delay capacitance	$C_{D}$	0	2.2	μF	_
PWM voltage	$V_{PWM}$	0	40	V	_
Junction temperature	$T_{j}$	-40	150	°C	_
Reference resistor	$R_{REF}$	0	1.8	Ω	_



### Table 4 Electrical Characteristics

 $V_{\rm I}$  = 13.5 V;  $R_{\rm REF}$  = 0.47  $\Omega$ ;  $V_{\rm PWM} \ge V_{\rm PWM,H}$ ; -40 °C <  $T_{\rm j}$  < 150 °C; all voltages with respect to ground; positive current defined flowing into pin; unless otherwise specified

Parameter	Symbol	Limit Values			Unit	<b>Test Condition</b>
		Min.	Тур.	Max.		
Current consumption off mode	$I_{qOFF}$	_	0.1	2	μΑ	$PWM = L,$ $T_{j} < 85  ^{\circ}C$
Current consumption	$I_{qL}$	_	12	22	mA	$V_{\rm Q} = 6.6 \; {\rm V}$
Output		•	•	•	•	
Output current	$I_{Q}$	357	376	395	mA	$V_{\rm Q}$ - $V_{\rm REF}^{-1)}$ = 6.6 V
		168	177	185	mA	$V_{\rm Q}$ - $V_{\rm REF}$ = 6.6 V; $R_{\rm REF}$ = 1.0 $\Omega$
		431	454	476	mA	$V_{\rm Q}$ - $V_{\rm REF}$ = 6.6 V; $R_{\rm REF}$ = 0.39 $\Omega$
		357	376	395	mA	5.4 V $\leq V_{Q}$ - $V_{REF} \leq$ 7.8 V; 9 V $\leq V_{I} \leq$ 16 V
Output current limit	$I_{Qmax}$	_	600	_	mA	$R_{REF} = 0 \ \Omega$
Drop voltage	$V_{dr}$	_	0.35	0.7	V	$I_{\rm Q} = 300 \; {\rm mA}$
PWM Input						
PWM high level	$V_{PWM,H}$	2.6	_	_	V	_
PWM low level	$V_{PWM,L}$	_	_	0.7	V	_
PWM input current high level	$I_{PWM,H}$	_	220	500	μΑ	V <sub>PWM</sub> = 5.0 V
PWM input current low level	$I_{PWM,L}$	-1	_	1	μΑ	$V_{PWM} = 0.0 V$
Turn on delay time	t <sub>PWM,ON</sub>	0	15	40	μs	70% of $I_{\rm Qnom}$ , see Figure 4
Turn off delay time	$t_{PWM,OFF}$	0	15	40	μs	30% of $I_{\text{Qnom}}$ , see Figure 4

Data Sheet 8 Rev. 1.0, 2004-01-01



## Table 4 Electrical Characteristics (cont'd)

 $V_{\rm I}$  = 13.5 V;  $R_{\rm REF}$  = 0.47  $\Omega$ ;  $V_{\rm PWM} \ge V_{\rm PWM,H}$ ; -40 °C <  $T_{\rm j}$  < 150 °C; all voltages with respect to ground; positive current defined flowing into pin; unless otherwise specified

Parameter	Symbol	Limit Values			Unit	Test Condition
		Min.	Тур.	Max.		
Reference						
Reference Voltage	$V_{REF}$	168	177	185	mV	$0.39 < R_{REF} < 1.0 \ \Omega$
Reference Input Current	$I_{REF}$	-1	0.1	1	μΑ	$V_{REF}$ = 180 mV
Status Output						
Lower status switching threshold	$V_{IQL}$	15	25	_	mV	ST = L
Upper status switching threshold	$V_{IQH}$	_	30	40	mV	ST = H
Status low voltage	$V_{STL}$	_	_	0.4	V	$I_{\rm ST}$ = 1.5 mA
Leakage current	$I_{STLK}$	_	_	5	μΑ	$V_{\mathrm{ST}}$ = 5.0 V
Status Delay						
Status reaction delay	$t_{STHL}$	6	10	14	ms	$C_{\rm D}$ = 47 nF, ST H $\rightarrow$ L
Status release delay	$t_{STLH}$	_	10	20	μs	$C_{\rm D}$ = 47 nF, ST L $\rightarrow$ H


<sup>1)</sup>  $V_{\rm Q}$  -  $V_{\rm REF}$  equals the forward voltage sum of the connected LEDs, see Figure 3.

Data Sheet 9 Rev. 1.0, 2004-01-01




## **Typical Performance Characteristics**


## **Output Current versus External Resistor**



## Reference Voltage versus Junction Temperature




## Output Current versus Supply Voltage






# **PWM Pin Input Current versus PWM Voltage**



# **PWM Pin Input Current versus PWM Voltage**



Data Sheet 11 Rev. 1.0, 2004-01-01



### **Package Outlines**




Figure 5 P-TO263-7-1 (Plastic Transistor Single Outline)

You can find all of our packages, sorts of packing and others in our Infineon Internet Page "Products": <a href="http://www.infineon.com/products">http://www.infineon.com/products</a>.

Dimensions in mm

#### Edition 2004-01-01

Published by Infineon Technologies AG, St.-Martin-Strasse 53, 81669 München, Germany
© Infineon Technologies AG 2004.

All Rights Reserved.

### Attention please!

The information herein is given to describe certain components and shall not be considered as a guarantee of characteristics.

Terms of delivery and rights to technical change reserved.

We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

#### Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

#### Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.