SCLS299A - JANUARY 1996 - REVISED MAY 1997

- Contain Four Flip-Flops With Double-Rail Outputs
- Applications Include:
 - Buffer/Storage Registers
 - Shift Registers
 - Pattern Generators
- Package Options Include Plastic Small-Outline (D), Thin Shrink Small-Outline (PW), and Ceramic Flat (W) Packages, Ceramic Chip Carriers (FK), and Standard Plastic (N) and Ceramic (J) 300-mil DIPs


description

These monolithic positive-edge-triggered D-type flip-flops have a direct clear (CLR) input. The 'HC175 feature complementary outputs from each flip-flop.


Information at the data (D) inputs meeting the setup time requirements is transferred to the outputs on the positive-going edge of the clock (CLK) pulse. Clock triggering occurs at a particular voltage level and is not directly related to the transition time of the positive-going edge of CLK. When CLK is at either the high or low level, the D input has no effect at the output.

The SN54HC175 is characterized for operation over the full military temperature range of –55°C to 125°C. The SN74HC175 is characterized for operation from –40°C to 85°C.

SN54HC175 . . . J OR W PACKAGE SN74HC175 . . . D, N, OR PW PACKAGE (TOP VIEW)



SN54HC175 . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

FUNCTION TABLE (each flip-flop)


| | INPUTS | OUTI | PUTS | |
|-----|------------|------|----------------|------------------|
| CLR | CLK | D | Q | Q |
| L | Х | Χ | L | Н |
| Н | \uparrow | Н | Н | L |
| Н | \uparrow | L | L | Н |
| Н | L | Χ | Q ₀ | \overline{Q}_0 |



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




logic symbol†



[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12. Pin numbers shown are for the D, J, N, PW, and W packages.

logic diagram (positive logic)



Pin numbers shown are for the D, J, N, PW, and W packages.

absolute maximum ratings over operating free-air temperature range‡

| Supply voltage range, V _{CC} | | 0.5 V to 7 V |
|--|-----------------|----------------|
| Input clamp current, I_{IK} ($V_I < 0$ or $V_I > V_{CC}$) (see | ee Note 1) | ±20 mA |
| Output clamp current, IOK (VO < 0 or VO > VC | C) (see Note 1) | ±20 mA |
| Continuous output current, I_O ($V_O = 0$ to V_{CC}) | | ±25 mA |
| Continuous current through V _{CC} or GND | | ±50 mA |
| Package thermal impedance, θ _{JA} (see Note 2) | : D package | 113°C/W |
| ••• | N package | |
| | PW package | |
| Storage temperature range, T _{sto} | | –65°C to 150°C |

[‡] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

^{2.} The package thermal impedance is calculated in accordance with JESD 51, except for through-hole packages, which use a trace length of zero.



NOTES: 1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

SCLS299A - JANUARY 1996 - REVISED MAY 1997

recommended operating conditions

| | | | SI | SN54HC175 | | | SN74HC175 | | |
|----------------|---------------------------------------|--------------------------|------|-----------|------|------|-----------|------|------|
| | | | MIN | NOM | MAX | MIN | NOM | MAX | UNIT |
| Vcc | Supply voltage | | 2 | 5 | 6 | 2 | 5 | 6 | V |
| | | V _{CC} = 2 V | 1.5 | | | 1.5 | | | |
| ViH | IH High-level input voltage | V _{CC} = 4.5 V | 3.15 | | | 3.15 | | | V |
| | | V _{CC} = 6 V | 4.2 | | | 4.2 | | | |
| | Low-level input voltage | V _{CC} = 2 V | 0 | | 0.5 | 0 | | 0.5 | V |
| V_{IL} | | V _{CC} = 4.5 V | 0 | | 1.35 | 0 | | 1.35 | |
| | | V _{CC} = 6 V | 0 | | 1.8 | 3 0 | | 1.8 | |
| VI | Input voltage | | 0 | | VCC | 0 | | VCC | V |
| Vo | Output voltage | | 0 | | VCC | 0 | | VCC | V |
| | | V _{CC} = 2 V | 0 | | 1000 | 0 | | 1000 | |
| t _t | Input transition (rise and fall) time | $V_{CC} = 4.5 \text{ V}$ | 0 | | 500 | 0 | | 500 | ns |
| | | V _{CC} = 6 V | 0 | | 400 | 0 | | 400 | |
| TA | Operating free-air temperature | | -55 | | 125 | -40 | | 85 | °C |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | | Vaa | Т | A = 25°C | ; | SN54HC175 | | SN74HC175 | | LINUT |
|----------------|----------------------|----------------------------|------------|------|----------|------|-----------|-------|-----------|-------|-------|
| PARAMETER | 1251 00 | CNDITIONS | vcc | MIN | TYP | MAX | MIN | MAX | MIN | MAX | UNIT |
| | | | 2 V | 1.9 | 1.998 | | 1.9 | | 1.9 | | |
| | | I _{OH} = -20 μA | 4.5 V | 4.4 | 4.499 | | 4.4 | | 4.4 | | |
| Voн | VI = VIH or VIL | | 6 V | 5.9 | 5.999 | | 5.9 | | 5.9 | | V |
| | | $I_{OH} = -4 \text{ mA}$ | 4.5 V | 3.98 | 4.3 | | 3.7 | | 3.84 | | |
| | | $I_{OH} = -5.2 \text{ mA}$ | 6 V | 5.48 | 5.8 | | 5.2 | | 5.34 | | |
| | | | 2 V | | 0.002 | 0.1 | | 0.1 | | 0.1 | |
| | | I _{OL} = 20 μA | 4.5 V | | 0.001 | 0.1 | | 0.1 | | 0.1 | |
| VOL | VI = VIH or VIL | | 6 V | | 0.001 | 0.1 | | 0.1 | | 0.1 | V |
| | | I _{OL} = 4 mA | 4.5 V | | 0.17 | 0.26 | | 0.4 | | 0.33 | |
| | | $I_{OL} = 5.2 \text{ mA}$ | 6 V | | 0.15 | 0.26 | | 0.4 | | 0.33 | |
| ΙĮ | $V_I = V_{CC}$ or 0 | | 6 V | | ±0.1 | ±100 | | ±1000 | | ±1000 | nA |
| Icc | $V_I = V_{CC}$ or 0, | I _O = 0 | 6 V | | | 8 | | 160 | | 80 | μΑ |
| C _i | | | 2 V to 6 V | | 3 | 10 | | 10 | | 10 | pF |

SN54HC175, SN74HC175 QUADRUPLE D-TYPE FLIP-FLOPS WITH CLEAR

SCLS299A – JANUARY 1996 – REVISED MAY 1997

timing requirements over recommended operating free-air temperature range (unless otherwise noted)

| | | | V | T _A = : | 25°C | SN54F | IC175 | SN74HC175 | | UNIT | |
|-------------------------------|------------------------------------|-----------------|-------|--------------------|------|-------|-------|-----------|------------------|------|--|
| | | | VCC | MIN | MAX | MIN | MAX | MIN | MAX | | |
| | f _{clock} Clock frequency | | 2 V | 0 | 6 | 0 | 4.2 | 0 | 5 | | |
| fclock | | | 4.5 V | 0 | 31 | 0 | 21 | 0 | 25 | MHz | |
| | | | 6 V | 0 | 36 | 0 | 25 | 0 | 29 | | |
| | | 2 V | 80 | | 120 | | 100 | | | | |
| | | CLR low | 4.5 V | 16 | | 24 | | 20 | | | |
| t _W Pulse duration | Dulas duration | | 6 V | 14 | | 20 | | 17 | | ns | |
| | ruise duration | CLK high or low | 2 V | 80 | | 120 | | 100 | | | |
| | | | 4.5 V | 16 | | 24 | | 20 | | | |
| | | | 6 V | 14 | | 20 | | 17 | | | |
| | | Data | 2 V | 100 | | 150 | | 125 | | ns | |
| | | | 4.5 V | 20 | | 30 | | 25 | | | |
| ۱. | Setup time before CLK↑ | | 6 V | 17 | | 25 | | 21 | | | |
| t _{su} | Setup time before CLK | | 2 V | 100 | | 150 | | 125 | | | |
| | | CLR inactive | 4.5 V | 20 | | 30 | | 25 | | | |
| | | | 6 V | 17 | | 25 | | 21 | | | |
| | | | 2 V | 0 | | 0 | | 0 | , and the second | ns | |
| th | Hold time, data after CLK↑ | | 4.5 V | 0 | | 0 | | 0 | | | |
| | | | 6 V | 0 | | 0 | | 0 | | | |

switching characteristics over recommended operating free-air temperature range, C_L = 50 pF (unless otherwise noted) (see Figure 1)


| DADAMETED | FROM | то | V | T, | λ = 25°C | ; | SN54H | IC175 | SN74H | C175 | LINUT |
|------------------|---------|----------|-------|-----|----------|-----|-------|-------|-------|------|-------|
| PARAMETER | (INPUT) | (OUTPUT) | VCC | MIN | TYP | MAX | MIN | MAX | MIN | MAX | UNIT |
| | | | 2 V | 6 | 12 | | 4.2 | | 5 | | |
| f _{max} | | | 4.5 V | 31 | 50 | | 21 | | 25 | | MHz |
| | | | 6 V | 36 | 60 | | 25 | | 29 | | |
| | CLR | Any | 2 V | | 52 | 150 | | 255 | | 190 | |
| | | | 4.5 V | | 15 | 30 | | 45 | | 38 | |
| | | | 6 V | | 13 | 26 | | 38 | | 32 | ns |
| ^t pd | | | 2 V | | 58 | 150 | | 255 | | 190 | 115 |
| | CLK | Any | 4.5 V | | 16 | 30 | | 45 | | 38 | |
| | | | 6 V | | 13 | 26 | | 38 | | 32 | |
| | | | 2 V | | 38 | 75 | | 110 | | 90 | |
| t _t | | Any | 4.5 V | | 8 | 15 | | 22 | | 19 | ns |
| | | | 6 V | | 6 | 13 | | 19 | | 16 | |

operating characteristics, $T_A = 25^{\circ}C$

| | PARAMETER | TEST CONDITIONS | TYP | UNIT |
|-----------------|---|-----------------|-----|------|
| C _{pd} | Power dissipation capacitance per flip-flop | No load | 30 | pF |



PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and test-fixture capacitance.

- B. Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_O = 50 \ \Omega$, $t_f = 6 \ ns$, $t_f = 6 \ ns$.
- C. For clock inputs, $f_{\mbox{max}}$ is measured when the input duty cycle is 50%.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. tpLH and tpHL are the same as tpd.

Figure 1. Load Circuit and Voltage Waveforms

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated