FAIRCHILD
SEMICONDUCTOR ™

FDN336P

Single P-Channel 2.5V Specified PowerTrench™ MOSFET

General Description

This P-Channel 2.5V specified MOSFET is produced using Fairchild Semiconductor's advanced PowerTrench process that has been especially tailored to minimize the on-state resistance and yet maintain low gate charge for superior switching performance.

These devices are well suited for portable electronics applications: load switching and power management, battery charging circuits, and DC/DC conversion.

Features

- -1.3 A, -20 V. $R_{DS(ON)} = 0.20\ \Omega$ @ $V_{GS} = -4.5$ V
  $R_{DS(ON)} = 0.27\ \Omega$ @ $V_{GS} = -2.5$ V.

- Low gate charge (3.6 nC typical).

- High performance trench technology for extremely low $R_{DS(ON)}$.

- High power version of industry standard SOT-23 package. Identical pin out to SOT-23 with 30% higher power handling capability.

SOT-23	**SuperSOT™-6**	**SuperSOT™-8**	**SO-8**	**SOT-223**	**SOIC-16**

SuperSOT™-3

Absolute Maximum Ratings $T_A = 25°C$ unless other wise noted

Symbol	Parameter		FDN336P	Units
V_{DSS}	Drain-Source Voltage		-20	V
V_{GSS}	Gate-Source Voltage		±8	V
I_D	Drain Current	- Continuous	-1.3	A
		- Pulsed	-10	
P_D	Maximum Power Dissipation	(Note 1a)	0.5	W
		(Note 1b)	0.46	
T_J, T_{STG}	Operating and Storage Temperature Range		-55 to +150	°C
THERMAL CHARACTERISTICS				
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	250	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	75	°C/W

Electrical Characteristics (T_A = 25 $^{\circ}$C unless otherwise noted)

Symbol	Parameter	Conditions		Min	Typ	Max	Units
OFF CHARACTERISTICS							
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS} = 0 V, I_D = -250 µA		-20			V
$\Delta BV_{DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	I_D = -250 µA, Referenced to 25 $^{\circ}$C			-16		mV /$^{\circ}$C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = -16 V, V_{GS} = 0 V				-1	µA
			T_J = 55°C			-10	µA
I_{GSSF}	Gate - Body Leakage, Forward	V_{GS} = 8 V, V_{DS} = 0 V				100	nA
I_{GSSR}	Gate - Body Leakage, Reverse	V_{GS} = -8 V, V_{DS}= 0 V				-100	nA
ON CHARACTERISTICS (Note 2)							
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS} = V_{GS}, I_D = -250 µA		-0.4	-0.9	-1.5	V
$\Delta V_{GS(th)}/\Delta T_J$	Gate Threshold Voltage Temp. Coefficient	I_D = -250 µA, Referenced to 25 $^{\circ}$C			3		mV /$^{\circ}$C
$R_{DS(ON)}$	Static Drain-Source On-Resistance	V_{GS} = -4.5 V, I_D = -1.3 A			0.122	0.2	Ω
			T_J =125°C		0.18	0.32	
		V_{GS} = -2.5 V, I_D = -1.1 A			0.19	0.27	
$I_{D(ON)}$	On-State Drain Current	V_{GS} = -4.5 V, V_{DS} = -5 V		-5			A
g_{FS}	Forward Transconductance	V_{DS} = -4.5 V, I_D = -2 A			4		S
DYNAMIC CHARACTERISTICS							
C_{iss}	Input Capacitance	V_{DS} = -10 V, V_{GS} = 0 V,			330		pF
C_{oss}	Output Capacitance	f = 1.0 MHz			80		pF
C_{rss}	Reverse Transfer Capacitance				35		pF
SWITCHING CHARACTERISTICS (Note 2)							
$t_{D(on)}$	Turn - On Delay Time	V_{DD} = -5 V, I_D = -0.5 A,			7	15	ns
t_r	Turn - On Rise Time	V_{GS} = -4.5 V, R_{GEN} = 6 Ω			12	22	ns
$t_{D(off)}$	Turn - Off Delay Time				16	26	ns
t_f	Turn - Off Fall Time				5	12	ns
Q_g	Total Gate Charge	V_{DS} = -10 V, I_D = - 2 A,			3.6	5	nC
Q_{gs}	Gate-Source Charge	V_{GS} = -4.5 V			0.8		nC
Q_{gd}	Gate-Drain Charge				0.7		nC
DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS							
I_S	Maximum Continuous Drain-Source Diode Forward Current					-0.42	A
V_{SD}	Drain-Source Diode Forward Voltage	V_{GS} = 0 V, I_S = -0.42 A (Note)			-0.7	-1.2	V

Note:

1. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.

a. 250°C/W when mounted on
a 0.02 in^2 pad of 2oz Cu.

b. 270°C/W when mounted on
 a 0.001 in^2 pad of 2oz Cu.

Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width $\leq$ 300µs, Duty Cycle $\leq$ 2.0%.

# Typical Electrical Characteristics

Figure 1. On-Region Characteristics.

**Figure 2. On-Resistance Variation with Drain Current and Gate**

**Figure 3. On-Resistance Variation with Temperature**.

Figure 4. On-Resistance Variation with Gate-to-Source Voltage.

Figure 5. Transfer Characteristics.

Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

## Typical Electrical Characteristics (continued)



Figure 7. Gate Charge Characteristics.

Figure 8. Capacitance Characteristics.


Figure 9. Maximum Safe Operating Area.

Figure 10. Single Pulse Maximum Power Dissipation.

Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1b.
Transient thermal response will change depending on the circuit board design.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™	ISOPLANAR™
CoolFET™	MICROWIRE™
CROSSVOLT™	POP™
E²CMOS™	PowerTrench™
FACT™	QS™
FACT Quiet Series™	Quite Series™
FAST®	SuperSOT™-3
FASTr™	SuperSOT™-6
GTO™	SuperSOT™-8
HiSeC™	TinyLogic™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.
As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The data sheet is printed for reference information only.