

晶创和立

GL4516


MINIATURE CADMIUM SULPHIDE PHOTOCONDUCTIVE CELL



FEATURES

- Miniature open frame package
- Epoxy coated
- Moisture resistant
- Spectral response similar to the human eye
- Applications include dusk-dawn lighting control

LIGHT DEPENDENT RESISTOR



Dimensions in millimetres

SPECIFICATION AND PERFORMANCE

Model	Vmax (VDC)	Pmax (mW)	Ambient temp(°C)	Spectral peak (nm)	Light Resistance at 10Lux (KΩ)	Dark Resistance (MΩ)	Gamm a value at 100- 10Lux	i Response Time (ms) i	
								Rise Time	Decay time
GL4516	150	100	-30~+70	540	5-10	0.5	0.6	20	30

Measuring Conditions

1. Light resistance:

Measured at 10 Lux with standard light A (2854K color temperature) and 2hr illumination at 400-600 lux prior to testing.

2. Dark Resistance:

Measured 10 senconds after closed 10 lux.

3. Gamma Characteristic:

Between 10 lux ande 100 lux and given by $\gamma = Ig(R10/R100)$

R10 R100 Cell resistance at 10 lux and 100 lux


The error of γ is \pm 0.1.


4. Pmax:

Max. power dissipation at ambient temperature of 25 $^{\circ}$ C.

5. Vmax:

Max. voltage in darkness that may be applied to the cell continuously.





SHENZHENSHI JINGCHUANGHELI TECHNOLOGY CO., LTD.

Tel:+86-755-33693441 Fax:+86-755-33693443

http://www.szjchl.com
E-mail:heli@szjchl.com