

308 Constitution Drive Menlo Park, CA 94025-1164 Phone: 800-227-4856

www.circuitprotection.com

PolySwitch® PTC Devices

Overcurrent Protection Device

PRODUCT: miniSMDC260F/16

DOCUMENT: SCD 25714 **REV LETTER: J** REV DATE: 15-Apr-11 PAGE NO.: 1 OF 1

Raychem Circuit Protection Products

Specification Status: Released

Maximum Electrical Rating


Voltage: 16V_{DC}

Short Circuit Current: 100A

Notes:

- 1. All terminations are tin plated.
- 2. Drawing not to scale

Marking:






TABLE I. DIMENSIONS:

	A		В		С		D		E
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
mm:	4.37	4.83	1.02	1.52	3.07	3.41	0.25	0.95	0.20
in:	(0.172)	(0.190)	(0.042)	(0.060)	(0.121)	(0.134)	(0.010)	(0.040)	(0.008)

TABLE II. PERFORMANCE RATINGS:

	CUF	RRENT	RATIN	GS**		TIME TO	RESISTANCE		TRIPPED-STATE	
						TRIP**	VALUES		POWER	
									DISSIPATION**	
AMPE	RES	AMPE	RES	AMPE	RES	SECONDS	OHMS		WATTS AT	
AT ()°C	AT 2	20°C	AT 6	0°C	AT 20°C, 8A	AT 20°C		20°C, 16V	
HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	MAX	MIN	MAX*	MAX	
3.0	6.2	2.6	5.0	2.0	4.0	5	0.015	0.05	1.2	

- * Maximum resistance is measured 1 hour after reflow
- ** Values Specified were determined using PCB's with 0.070"X1.5 ounce copper traces.

UL, CSA, TÜV Agency Recognitions: Reference Documents: PS300

Precedence: This specification takes precedence over documents referenced herein.

Reference documents shall be the issue in effect on the date of invitation for bid. Effectivity:

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

Directive 2002/95/EC Compliant

ELV Compliant

Directive 2000/53/EC Compliant







© 2005, 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

^{*} Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm