

# **OP07x Precision Operational Amplifiers**

Check for Samples: OP07C, OP07D


#### **FEATURES**

- Low Noise
- No External Components Required
- Replace Chopper Amplifiers at a Lower Cost
- Wide Input-Voltage Range: 0 to ±14 V Typ
- Wide Supply-Voltage Range: ±3 V to ±18 V


#### DESCRIPTION

These devices offer low offset and long-term stability by means of a low-noise, chopperless, bipolar-inputtransistor amplifier circuit. For most applications, external components are not required for offset nulling and frequency compensation. The true differential input, with a wide input-voltage range and outstanding common-mode rejection, provides maximum flexibility and performance in high-noise environments and in noninverting applications. Low bias currents and extremely high input impedances are maintained over the entire temperature range. The OP07 devices are unsurpassed for low-noise, high-accuracy amplification of very-low-level signals.

These devices are characterized for operation from 0°C to 70°C.




NC-No internal connection





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.





Current values shown are nominal.



#### **Absolute Maximum Ratings**

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V <sub>CC+</sub> <sup>(2)</sup>	Cumply yeltogo			22	V
$\frac{V_{CC+}^{(2)}}{V_{CC-}^{(2)}}$	Supply voltage		-22	V	
	Differential input voltage (3)			±30	V
V <sub>I</sub>	Input voltage range (either input) (4)		±22	V	
	Duration of output short circuit <sup>(5)</sup>	(5)			
1	Package thermal impedance, junction to free air (6)(7)	D package		97	°C/W
$\theta_{JA}$	rackage thermal impedance, junction to free all ****		85	C/VV	
ГЈ	Operating virtual-junction temperature			150	°C
	Lead temperature 1,6 mm (1/16 in) from case for 10 s			260	°C
T <sub>stg</sub>	Storage temperature range		-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- All voltage values, unless otherwise noted, are with respect to the midpoint between  $V_{CC+}$  and  $V_{CC-}$
- Differential voltages are at IN+ with respect to IN-.
- The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 V, whichever is less.
- The output may be shorted to ground or to either power supply.
- Maximum power dissipation is a function of  $T_{J(max)}$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_{J(max)} T_A)/\theta_{JA}$ . Selecting the maximum of 150°C can affect reliability. The package thermal impedance is calculated in accordance with JESD 51-7.

### **Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
$V_{CC\pm}$	Supply voltage		±3	±18	V
$V_{IC}$	Common-mode input voltage	$V_{CC\pm} = \pm 15 \text{ V}$	-13	13	V
T <sub>A</sub>	Operating free-air temperature	•	0	70	°C

Product Folder Links: OPO7C OPO7D



#### **Electrical Characteristics**

at specified free-air temperature,  $V_{CC\pm} = \pm 15 \text{ V}$  (unless otherwise noted)<sup>(1)</sup>

	DARAMETER	TEST CO	<b>T</b> (2)		OP07C			OP07D				
PARAMETER		TEST CO	T <sub>A</sub> <sup>(2)</sup>	MIN TYP		MAX	MIN	TYP	MAX	UNIT		
V	l	V 0.V	D 500	25°C		60				150	\/	
$V_{IO}$	Input offset voltage	V <sub>O</sub> = 0 V	$R_S = 50\Omega$	0°C to 70°C		85				250	μV	
$\alpha_{VIO}$	Temperature coefficient of input offset voltage	V <sub>O</sub> = 0 V	$R_S = 50\Omega$	0°C to 70°C		0.5				2.5	μV/°C	
	Long-term drift of input offset voltage	See <sup>(3)</sup>				0.4					μV/mo	
	Offset adjustment range	$R_S = 20 \text{ k}\Omega$	See Figure 1	25°C		±4					mV	
	Input offset current			25°C		8.0				6	nA	
I <sub>IO</sub>	input onset current			0°C to 70°C		1.6				8	IIA	
$\alpha_{\text{IIO}}$	Temperature coefficient of input offset current			0°C to 70°C		12				50	pA/°C	
	Input higo ourrant			25°C	±1.8 ±2.2				±12	nA		
I <sub>IB</sub>	Input bias current			0°C to 70°C			±14			IIA		
$\alpha_{IIB}$	Temperature coefficient of input bias current			0°C to 70°C		18				50	pA/°C	
\/	Common-mode input			25°C	±13	±14		±13	±14		V	
$V_{ICR}$	voltage range			0°C to 70°C	±13	±13.5		±13	±13.5		V	
	Peak output voltage	$R_{L} \ge 10 \text{ k}\Omega$ $R_{L} \ge 2 \text{ k}\Omega$		25°C	±12	±13		±12	±13			
\/					±11.5	±12.8		±11.5	±12.8		V	
$V_{OM}$		$R_L \ge 1 \text{ k}\Omega$				±12			±12		V	
		$R_L \ge 2 \ k\Omega$		0°C to 70°C	±11	±12.6		±11	±12.6			
	Large-signal differential	$V_{CC} = 15 \text{ V}, V_{O} = R_{L} \ge 500 \text{ k}\Omega$	= 1.4 V to 11.4 V,	25°C	100	400			400			
$A_{VD}$	voltage amplification	V 40 D 010		25°C	120	400		120	400		V/mV	
		$V_0 = \pm 10, R_L = 2$	2K22	0°C to 70°C	100	400		100	400			
B <sub>1</sub>	Unity-gain bandwidth			25°C	0.4	0.6		0.4	0.6		MHz	
ri	Input resistance			25°C	8	33		7	31		ΜΩ	
CMDD	Common-mode	V .42 V D	500	25°C	100	120		94	110		٩D	
CMRR	rejection ratio	$V_{IC} = \pm 13 \text{ V}, R_S = 50\Omega$		0°C to 70°C	97	120		94	106		dB	
k	Supply-voltage sensitivity	V2.V /= .	10 V P 500	25°C		7	32		7	32	\/\/	
k <sub>SVS</sub>	$(\Delta V_{IO}/\Delta V_{CC})$	$V_{CC+} = \pm 3 \text{ V to } \pm 18 \text{ V}, R_S = 50\Omega$		0°C to 70°C		10	51		10	51	μV/V	
D	Dawer dissination	V <sub>O</sub> = 0, No load		0500		80	150		80	150	mW	
$P_D$	Power dissipation	$V_{CC+} = \pm 3 \text{ V}, V_{O}$	25°C		4	8		4	8			

Since long-term drift cannot be measured on the individual devices prior to shipment, this specification is not intended to be a warranty. It is an engineering estimate of the averaged trend line of drift versus time over extended periods after the first 30 days of operation. All characteristics are measured with zero common-mode input voltage, unless otherwise specified.

The package thermal impedance is calculated in accordance with JESD 51-7.



## **Operating Characteristics**

at specified free-air temperature,  $V_{CC} = 5 \text{ V}$  (unless otherwise noted)

	PARAMETER	TEST CONDITIONS <sup>(1)</sup>	OP07C	OP07D	UNIT		
	PARAMETER	TEST CONDITIONS	TYP	TYP	UNII		
		f = 10 Hz	10.5	10.5			
$V_n$	1	f = 100 Hz	10.2	10.3	nV/√ <del>Hz</del>		
		f = 1 kHz	9.8	9.8	8		
V <sub>N(PP)</sub>	Peak-to-peak equivalent input noise voltage	f = 0.1 Hz to 10 Hz	0.38	0.38	μV		
		f = 10 Hz	0.35	0.35			
In	Equivalent input noise current	f = 100 Hz	0.15	0.15	nV/√ <del>Hz</del>		
		f = 1 kHz	0.13	0.13			
I <sub>N(PP)</sub>	Peak-to-peak equivalent input noise current	f = 0.1 Hz to 10 Hz	15	15	pA		
SR	Slew rate	$R_L \ge 2 k\Omega$	0.3	0.3	V/µs		

(1) All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise noted.

#### **APPLICATION INFORMATION**




Figure 1. Input Offset-Voltage Null Circuit



## **REVISION HISTORY**

CI	hanges from Revision E (May 2004) to Revision F	Page
•	Updated document to new TI data sheet format - no specification changes.	1
•	Deleted Ordering Information table.	1

Submit Documentation Feedback





10-Jun-2014

#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type		Pins	-	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
OP-07DPSR	ACTIVE	SO	PS	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP-07D	Samples
OP-07DPSRG4	ACTIVE	so	PS	8	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP-07D	Samples
OP07CD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07C	Samples
OP07CDE4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07C	Samples
OP07CDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07C	Samples
OP07CDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU   CU SN	Level-1-260C-UNLIM	0 to 70	OP07C	Samples
OP07CDRE4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07C	Samples
OP07CDRG4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07C	Samples
OP07CP	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	OP07CP	Samples
OP07CPE4	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	OP07CP	Samples
OP07DD	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07D	Samples
OP07DDG4	ACTIVE	SOIC	D	8	75	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07D	Samples
OP07DDR	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07D	Samples
OP07DDRE4	ACTIVE	SOIC	D	8	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	OP07D	Samples
OP07DP	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	OP07DP	Samples
OP07DPE4	ACTIVE	PDIP	Р	8	50	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	OP07DP	Samples

<sup>(1)</sup> The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.



#### PACKAGE OPTION ADDENDUM

10-Jun-2014

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free** (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# PACKAGE MATERIALS INFORMATION

www.ti.com 18-Apr-2014

## TAPE AND REEL INFORMATION





_		
		Dimension designed to accommodate the component width
		Dimension designed to accommodate the component length
		Dimension designed to accommodate the component thickness
	W	Overall width of the carrier tape
Γ	P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

All ulmensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
OP-07DPSR	SO	PS	8	2000	330.0	16.4	8.2	6.6	2.5	12.0	16.0	Q1
OP07CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
OP07CDRG4	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
OP07DDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1

www.ti.com 18-Apr-2014



\*All dimensions are nominal

7 th difficients are frominal							
Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
OP-07DPSR	SO	PS	8	2000	367.0	367.0	38.0
OP07CDR	SOIC	D	8	2500	340.5	338.1	20.6
OP07CDRG4	SOIC	D	8	2500	340.5	338.1	20.6
OP07DDR	SOIC	D	8	2500	340.5	338.1	20.6

# P (R-PDIP-T8)

# PLASTIC DUAL-IN-LINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MS-001 variation BA.



# D (R-PDSO-G8)

## PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AA.



# D (R-PDSO-G8)

# PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.





NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



#### IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

#### Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom Amplifiers amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors <a href="https://www.ti.com/omap">www.ti.com/omap</a> TI E2E Community <a href="https://example.com/omap">e2e.ti.com/omap</a>

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>