JIANGSU CHANGJIANG ELECTRONICS TECHNOLOGY CO.,LTD

SOT-23 Plastic-Encapsulate Transistors

MMBT3906 TRANSISTOR (PNP)

SOT－23



1. BASE
2. EMITTER
3. COLLECTOR

FEATURES

- As complementary type, the NPN transistor MMBT3904 is Recommended
- Epitaxial planar die construction

MARKING: 2A

MAXIMUM RATINGS (T_A=25℃ unless otherwise noted)

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	-40	V
V_{CEO}	Collector-Emitter Voltage	-40	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current -Continuous	-0.2	A
P_C	Collector Dissipation	0.2	W
$R_{\theta JA}$	Thermal resistance junction to ambient	625	℃/W
T_J	Junction Temperature	150	℃
T_{stg}	Storage Temperature	-55~+150	℃

ELECTRICAL CHARACTERISTICS (Tamb=25℃ unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	I_C=-10μA, I_E=0	-40		V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	I_C= -1mA, I_B=0	-40		V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	I_E= -10μA, I_C=0	-5		V
Collector cut-off current	I_{CBO}	V_{CB}= -40 V, I_E=0		-100	nA
Collector cut-off current	I_{CEX}	V_{CE}=-30V, $V_{BE(off)}$=-3V		-50	nA
Emitter cut-off current	I_{EBO}	V_{EB}= -5V, I_C=0		-100	nA
DC current gain	h_{FE1}	V_{CE}=-1V, I_C= -10mA	100	300	
	h_{FE2}	V_{CE}= -1V, I_C=-50mA	60		
	h_{FE3}	V_{CE}= -1V, I_C=-100mA	30		
Collector-emitter saturation voltage	$V_{CE(sat)1}$	I_C=-50mA, I_B=-5mA		-0.3	V
Base-emitter saturation voltage	$V_{BE(sat)}$	I_C= -50mA, I_B=-5mA		-0.95	V
Transition frequency	f_T	V_{CE}=-20V,I_C=-10mA,f=100MHz	300		MHz
Delay Time	td	V_{CC}=-3V,V_{BE}=-0.5V I_C=-10mA, I_{B1}=I_{B2}=-1mA		35	nS
Rise Time	tr			35	nS
Storage Time	ts	V_{CC}=-3V,I_C=-10mA I_{B1}=I_{B2}=-1mA		225	nS
Fall Time	tf			75	nS

CLASSIFICATION OF $h_{FE(1)}$

HFE	100-300	
RANK	L	H
RANGE	100－200	200－300

D,May,2012

Typical Characterisitics MMBT3906

















D,May,2012