






MAPX	MODIFICATION	DATE
------	--------------	------



- Specification:**
- 1. Electrical Characteristics:**
 Dielectric Withstanding Voltage: AC 500V/1MINUTE.
 Insulation Resistance: 1000 MΩ/Min.
 Contact Resistance: 30 mΩ Max.
- 2. Mechanical Characteristics:**
 INSERTION FORCE: 30N(3.06kgf) MAX
 EXTRACTION FORCE: 10-30N(1.02-3.06kgf)
 Durability: 1500cycles, EXTRACTION FORCE: 10-30N(1.02-3.06kgf)
- 3. Material:**
 Terminal: Phosphor Bronze, C5191/C2680R-EH T=0.25
 Plating: Gold 0.76 um Min plating over 1.27 um Min Nickel underplate, 2.54 um Min Sn selective plating on solder tail;
 Shell: Bronze, C2680R-H=0.30mm
 Plating: Nickel underplate 2.54 um Min;
 Housing: LCP Black
- 4. Environmental:**
 Operating Temperature: 0°C to +85°C.

产品图
PRODUCT CHART DWG

公差一览表		单位		制图		制图料号	
TOLERANCE UNLESS OTHERWISE	UNITS	MM	DRAWING	Z-Y-B	PRODUCT PART NO		
X ±0.25	X	±5°	比例	1:1	产品名称	USB 短体180插板外壳	
X ±0.20	X	±2°	日期	2011.09.01	审核	版本	
XX ±0.15	XX	±1°	DATE	2011.09.01	核准	AD	
XXX ±0.10	XXX	±0.5°	DATE	2011.09.01	APRD		