





GU (General Use)-E Type 2-Channel (Form A) Type

PhotoMOS RELAYS



mm inch



FEATURES

1. Reinforced insulation **5,000** V type More than 0.4 mm internal insulation distance between inputs and outputs. Conforms to EN41003, EN60950 (reinforced insulation).

2. Compact 8-pin DIP size

The device comes in a compact (W)6.4×(L)9.86×(H)3.2 mm (W).252×(L).388×(H).126 inch, 8-pin DIP size (through hole terminal type).

- 3. Applicable for 2 Form A use as well as two independent 1 Form A use
- **4. Controls low-level analog signals**PhotoMOS relays feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without

5. High sensitivity, high speed response.

Can control a maximum 0.14 A load current with a 5 mA input current. Fast operation speed of 0.5 ms (typical). (AQW210EH)

6. Low-level off state leakage current

TYPICAL APPLICATIONS

- Modem
- Telephone equipment
- Security equipment
- Sensors

TYPES

Туре	I/O isolation voltage	Output rating*		Part No.					
				Through hole terminal	Surface-mount terminal			Packing quantity	
		Lood	Load Load			Tape and reel packing style			Tape and reel
		Load Load voltage current	Tube packing style		Picked from the 1/2/3/4-pin side	Picked from the 5/6/7/8-pin side	Tube		
AC/DC type	Reinforced 5,000 V	350 V	120 mA	AQW210EH	AQW210EHA	AQW210EHAX	AQW210EHAZ	1 tube contains 40 pcs.	
		400 V	100 mA	AQW214EH	AQW214EHA	AQW214EHAX	AQW214EHAZ	1 batch contains 400 pcs.	

^{*}Indicate the peak AC and DC values.

Note:

distortion.

RATING

1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)

Item		Symbol	AQW210EH (A)	AQW214EH (A)	Remarks	
Input	LED forward current		lF	50mA		
	LED reverse voltage		VR	3V		
	Peak for	Peak forward current		1A		f =100 Hz, Duty factor = 0.1%
	Power dissipation		Pin	75mW		
Output	Load vol	tage (peak AC)	VL	350 V	400 V	
	Continuous load current (peak AC)		l _L	0.12 A (0.14 A)	0.1 A (0.13 A)	Peak AC, DC (): in case of using only 1 channel
	Peak load current		Ipeak	0.36 A	0.3 A	100 ms (1 shot), V _L = DC
	Power dissipation		Pout	800mW		
Total power dissipation		P⊤	850mW			
I/O isolation voltage		Viso	5,000 V AC			
iomporataro iiii		Operating	Topr	-40°C to +85°C −40°F to +185°F		Non-condensing at low temperatures
		Storage	T _{stg}	-40°C to +100°C -40°F to +212°F		

For space reasons, the SMD terminal shape indicator "A" and the package type indicator "X" and "Z" are omitted from the seal.

AQW21OEH


2. Electrical characteristics (Ambient temperature: 25°C 77°F)

	Item		Symbol	AQW210EH (A)	AQW214EH (A)	Condition
Input	LED oper- ate current	Typical	1-	1.2	I∟=Max.	
		Maximum	Fon	3.0	IL=IVIAX.	
	LED turn off current	Minimum	Foff	0.4	IL=Max.	
		Typical	I Foff	1.1	IL=IVIAX.	
	LED drop-	Typical	VF	1.14 (1.25 V	I=5mA	
	out voltage	Maximum	VF	1.5		
Output	On resis- tance	Typical	Ron	18Ω	26Ω	I _F =5mA I _L =Max.
		Maximum		25Ω	35Ω	Within 1 s on time
	Off state leakage current	Maximum	Leak	1μΑ		I⊧=0mA V∟=Max.
Transfer character- istics	Turn on time*	Typical	Ton	0.5	I=5mA	
		Maximum	l on	2.0	I∟=Max.	
	Turn off time*	Typical	Toff	0.08	I _F =5mA	
		Maximum	I off	1.0	I∟=Max.	
	I/O capaci- tance	Typical	Ciso	0.8	f =1MHz	
		Maximum	Ciso	1.5	V _B =0	
	Initial I/O isolation resistance	Minimum	Riso	1,000	500V DC	

Note: Recommendable LED forward current IF= 5 to 10mA.

For type of connection, see page 32.

*Turn on/Turn off time




- **■** For Dimensions, see Page 27.
- For Schematic and Wiring Diagrams, see Page 32.
- For Cautions for Use, see Page 36.

REFERENCE DATA


1. Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40°C to +85°C -40°F to +185°F




2. On resistance vs. ambient temperature char-

Measured portion: between terminals 5 and 6, 7 and 8; LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




3. Turn on time vs. ambient temperature characteristics

Sample: All types LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




4. Turn off time vs. ambient temperature characteristics

Sample: All types LED current: 5 mA; Load voltage: Max. (DC); Continuous load current: Max. (DC)




5. LED operate current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)




6. LED turn off current vs. ambient temperature characteristics

Sample: All types; Load voltage: Max. (DC); Continuous load current: Max. (DC)




7. LED dropout voltage vs. ambient temperature characteristics

Sample: All types; LED current: 5 to 50 mA




8. Voltage vs. current characteristics of output at MOS portion

Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F



9. Off state leakage current


Measured portion: between terminals 5 and 6, 7 and 8; Ambient temperature: 25°C 77°F



10. LED forward current vs. turn on time characteristics

Sample: All types


Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



11. LED forward current vs. turn off time characteristics

Sample: All types

Measured portion: between terminals 5 and 6, 7 and 8; Load voltage: Max. (DC); Continuous load current: Max. (DC); Ambient temperature: 25°C 77°F



12. Applied voltage vs. output capacitance characteristics

Sample: All types

Measured portion: between terminals 5 and 6, 7 and 8; Frequency: 1 MHz; Ambient temperature: 25°C 77°F

