





D款, 正向10.6前两脚, SMT-*6.50

MAPX

MODIFICATION

DATE



NOTES:

- 1.HOUSING: SEE NOTES, UL94V-0 .
TERMINAL: SEE NOTES.
SHELL: SEE NOTES.

SPECIFICATION:


- 1.ELECTRICAL CHARACTERISTIC:
CONTACT RESISTANCE: 30MΩ MAX
DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN
INSULATION RESISTANCE: 1000MΩ MIN
2.MECHANICAL CHARACTERISTIC:
INSERTION FORCE: 35N(3.57KGF) MAX
EXTRACTION FORCE: 10~35N(1.02~3.57KGF)MIN
DURABILITY: 1500 CYCLES EXTRACTION FORCE:10~35N
5000 CYCLES MIN
5000 CYCLES EXTRACTION FORCE:3~35N

3.ENVIRONMENTAL:

OPERATING TEMPERATURE: -55℃+85℃

4.Contact finish:

- 01:Selective Gold Flash
02:Selective Gold 3U"
03:Selective Gold 5U"
04:Selective Gold 15U"
05:Selective Gold 30U"



FRONT EDGE OF CONNECTOR
PCB LAYOUT (T=1.60mm)

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.15	X.	±5°
.X	±0.10	.X	±2°
.XX	±0.05	.XX	±1°
.XXX	±0.03	.XXX	±0.5°

单位

UNITS

MM

制图

DRAWING

Z-Y-B

制图料号

PRODUCT PART NO

JTJ-USB-10.6-002

比例

SCALE

1:1

审核

CHKD

产品名称

PRODUCT NAME

USB A/F 10.6无边前两脚鱼叉(方弹)

日期

DATE

2012.09.24

核准

APPD

角法

VIEW

版本

VER

AD

AD