




MAPX	MODIFICATION	DATE



NOTES:

1. HOUSING: SEE NOTES,
- TERMINAL: SEE NOTES.
- SHELL: SEE NOTES.

SPECIFICATION:

1. ELECTRICAL CHARACTERISTIC:

- CONTACT RESISTANCE: 30MΩ MAX
- DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN
- INSULATION RESISTANCE: 1000MΩ MIN

2. MECHANICAL CHARACTERISTIC:

- INSERTION FORCE: 35N(3.57KGF) MAX
- EXTRACTION FORCE: 10~35N(1.02~3.57KGF) MIN
- DURABILITY: 1500 CYCLES EXTRACTION FORCE: 10~35N  
5000 CYCLES MIN
- 5000 CYCLES EXTRACTION FORCE: 3~35N

3. ENVIRONMENTAL:

- OPERATING TEMPERATURE: -55°C+85°C

4. Contact finish:

- 01: Selective Gold Flash
- 02: Selective Gold 3U"
- 03: Selective Gold 5U"
- 04: Selective Gold 15U"
- 05: Selective Gold 30U"

产品图 PRODUCT CHART DWG				单位 UNITS		制图 DRAWING		Z-Y-B		制图料号 PRODUCT PART NO.	
公差一览表 TOLERANCE UNLESS OTHERWISE				MM		审核 CHKD				产品名称 PRODUCT NAME	
X.	±0.25	X.	±5°	比例 SCALE		日期 DATE		2012.10.15		C42515	
.X	±0.20	.X	±2°	核准 APPD		角法 VIEW		版本 VER		AD	
.XX	±0.15	.XX	±1°								
.XXX	±0.10	.XXX	±0.5°								