




MAPX	MODIFICATION	DATE







FRONT EDGE OF CONNECTOR
PCB LAYOUT

- NOTES:
1. HOUSING: SEE NOTES,
TERMINAL: SEE NOTES,
SHELL: SEE NOTES.
- SPECIFICATION:
1. ELECTRICAL CHARACTERISTIC:
CONTACT RESISTANCE: 30MΩ MAX
DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN
INSULATION RESISTANCE: 1000MΩ MIN
2. MECHANICAL CHARACTERISTIC:
INSERTION FORCE: 35N(3.57KGF) MAX
EXTRACTION FORCE: 10~35N(1.02~3.57KGF)MIN
DURABILITY: 1500 CYCLES EXTRACTION FORCE:10~35N
3000 CYCLES MIN
5000 CYCLES EXTRACTION FORCE:3~35N
3. ENVIRONMENTAL:
OPERATING TEMPERATURE: -55°C+85°C
4. Contact finish:
01:Selective Gold Flash
02:Selective Gold 3U"
03:Selective Gold 5U"
04:Selective Gold 15U"
05:Selective Gold 30U"



SECTION A-A



<p>产品图 PRODUCT CHART DWG</p> <p>公差一览表 TOLERANCE UNLESS OTHERWISE</p>				<p>单位 UNITS</p> <p>MM</p>	<p>制图 DRAWING</p> <p>Z-Y-B</p>	<p>制图料号 PRODUCT PART NO.</p> <p>JTJ-USB AF 10.0-C-009</p>	<p>产品名称 PRODUCT NO.</p> <p>USB A/F 180° (10.0)无卷边</p>	<p>版本 VER</p> <p>A0</p>
X.	±0.25	X.	±5.°					
.X	±0.20	.X	±2.°					
.XX	±0.15	.XX	±1.°					
.XXX	±0.10	.XXX	±0.5°					
日期 DATE	2012.06.15	核准 APPD	角法 VIEW					