


◆ SPECIFICATIONS

Unit:mm

- ◇ Poles: 3~5
- ◇ Applicable wire: AWG#28-#20
- ◇ Voltage rating: 300V DC/AC
- ◇ Current rating: 9A
- ◇ Withstand voltage: 1500V AC
- ◇ Working Temperature: -25°C ~ +85°C
- ◇ Insulation resistance:  $\geq 1000M\Omega$
- ◇ Contact resistance:  $\leq 0.015\Omega$
- ◇ Applicable PC board thickness: 1.6mm



Poles	Type	Size(mm)	
		A	B
3	5557-3P	8.40	14.00
4	5557-4P	12.60	18.20
5	5557-5P	16.80	22.40

# 产品图片

