

项目	零件名称	数量	材质	处理/备注
1	SHELL	1	STAINLESS	Ni:50u"
2	Molding HOUSING	2	L.C.P	(Black)
3	GND SPRING	2	STAINLESS	Ni:50u"
4	Insert molding 12PIN	2	L.C.P	(Black)
5	CONTACT	24	COPPER ALLOY	Contact area: gold flash, Solder tails: Tn100u", Ni:50u"
6	PCB	1		

: SPECIFICATION

MATERIAL

See drawing
STANDARD DATA

Operating temperature: $-10^{\circ}\text{C} \sim +60^{\circ}\text{C}$
Storage temperature: $-20^{\circ}\text{C} \sim +85^{\circ}\text{C}$

ELECTRICAL

Insulator resistance: 100Mohms Min.

Withstanding voltage: 100 VAC / minute

Contact resistance: initial 40mohms Max;





after 50mohms Max.

MECHANICAL

Mating force: 5~20N

Umating force : 8~20N

Durability: 5000 cycles Min.



产品图
PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

公差	公差一览表	单位	MM	制图	Z-Y-B	产品料号	角法	版本	A0
X	±0.25	UNITS	MM	DRAWING	Z-Y-B	PRODUCT PART NO.	USP-3.1 公头/双面POP板转micro有边	版本	A0
X	±0.20	SCALE	1:1	审核					
XX	±0.15	SCALE		核准	郭治富				
.XXX	±0.10	DATE	2015.07.14	APPD					