

POWER MANAGEMENT

High-Voltage EL Lamp Driver

The IMP803 is an Electroluminescent (EL) lamp driver with the four EL lamp driving functions on-chip. These are the switch-mode power supply, its high-frequency oscillator, the high-voltage H-bridge lamp driver and its low-frequency oscillator. The IMP803 drives EL lamps of up to 30nF capacitance to high brightness; EL lamps with capacitances greater than 30nF can be driven, but will be lower in light output. The typical regulated output voltage that is applied to the EL lamp is 180V peak-to-peak. The circuit requires few external components, a single inductor, single diode, two capacitors and three resistors. Two of these resistors set the frequency for two internal oscillators.

The IMP803 operates over a 2.0V to 6.5V supply voltage range. A regulated, low-power source can supply the low quiescent current of the IMP803. The inductor may be driven from an independent, unregulated supply voltage in dual supply applications.

An internal circuit shuts down the switching regulator when the lamp drive voltage reaches 180V peak-to-peak. This conserves power and extends battery life.

The IMP803 is available in MicroSO and SO-8 packages and in die or wafer form.


Key Features

- ◆ Low Power: 420µA typical V_{DD} current
- ◆ Wide operating voltage range from 2.0V to 6.5V
- ◆ 180V peak-to-peak typical AC output voltage
- Large output load capability drive lamps with more than 30nF capacitance
- Adjustable output lamp frequency for control of lamp color, lamp life, and power consumption
- Adjustable converter frequency to minimize power consumption
- ◆ Device can be Enabled/Disabled
- ◆ Low quiescent current 20nA (disabled)
- High-Voltage CMOS Process
- MicroSO package option

Applications

- ◆ GPS units/Pagers/Cellular phones
- ◆ PDAs/Handheld computers
- Safety illumination
- ◆ Portable instrumentation
- Battery-operated displays
- LCD modules
- Toys


Block Diagram





Pin Configuration

SO/ MicroSO



Pin Compatible With HV803 and IMP560

Ordering Information

| Part Number | Input Voltage | Regulated Output Voltage | Temperature Range | Pins-Package |
|-------------|---------------|--------------------------|-------------------|--------------|
| IMP803LG | 2.0V to 6.5V | Yes | −40°C to +85°C | 8-SO |
| IMP803IMA | 2.0V to 6.5V | Yes | -40°C to +85°C | 8-MicroSO |
| IMP803SX* | 2.0V to 6.5V | Yes | 25°C | Dice |
| IMP803/D1** | 2.0V to 6.5V | Yes | 25°C | Dice |

^{*} Disable pad not active

Add /T to ordering part number for Tape and Reel.

Absolute Maximum Ratings

| V_{DD} , $V_{RSW\text{-OSC}}$ and $V_{REL\text{-OSC}}$ |
|--|
| V_{CS} , L_X |
| Operating Temperature Range40°C to +85°C |
| Storage Temperature Range65°C to +150°C |
| Power Dissipation (SO) 400mW |
| Power Dissipation (MicroSO) 300mW |
| V_A , V_B |

Note: All voltages are referenced to GND.

These are stress ratings only and functional operation is not implied. Exposure to absolute maximum ratings for prolonged time periods may affect device reliability.

Electrical Characteristics

Unless otherwise noted, V_{DD} = 3.0V, R_{SW} = 750k Ω , R_{EL} = 2.0M Ω , and T_A = 25°C.

| Parameter | Symbol | Conditions | Min | Тур | Max | Units |
|--|---------------------|--------------------------------------|-----|-----|-----|-------|
| ON-resistance of MOS Switch | R _{DS(ON)} | I = 100mA | | 3.5 | 8 | Ω |
| Output Voltage Regulation | V _{CS} | V _{DD} = 2.0 to 6.5V | 80 | 90 | 100 | V |
| Output Voltage Peak-to-peak (in regulation) | V_A - V_B | V _{DD} = 2.0 to 6.5V | 160 | 180 | 200 | V |
| Quiescent V _{DD} Supply Current, Disabled | I _{DDQ} | V _{RSW-OSC} < 100mV | | 20 | 200 | nA |
| Input Current at V _{DD} Pin | I_{DD} | V _{DD} = 3.0V, See Figure 1 | | 420 | 700 | μA |
| Input Current at V _{DD} Pin | I _{DD} | V _{DD} = 5.0V, See Figure 2 | | 500 | 750 | μΑ |
| Input Current: I _{DD} Plus Inductor Current | I _{IN} | V _{DD} = 3.0V, See Figure 1 | | 20 | 31 | mA |
| Output Voltage at V _{CS} | V _{CS} | V _{DD} = 3.0V, See Figure 1 | 60 | 74 | 100 | V |
| V _{A-B} Output Drive Frequency | f_{EL} | V _{DD} = 3.0V, See Figure 1 | 300 | 370 | 430 | Hz |
| Switching Frequency | f _{SW} | V _{DD} = 3.0V, See Figure 1 | 50 | 70 | 90 | kHz |
| Switching Duty Cycle | D _{SW} | V _{DD} = 3.0V, See Figure 1 | | 88 | | % |


3)


^{**} Disable pad active








Typical Characteristics
















Pin Descriptions

| Pin Number | Name | Function | |
|------------|---------------------|---|--|
| 1 | V_{DD} | Positive voltage supply for the IMP803. Inductor L may be connected here or to a separate unregulated supply. | |
| 2 | R _{SW-OSC} | Switch-mode resistor pin. Switching frequency is determined by an external resistor, R _{SW} . | |
| 3 | C _S | Boost converter storage capacitor. The voltage across the EL lamp is equal to twice the voltage at $C_{\rm S}$. | |
| 4 | L _X | Connection to flyback inductance, L. | |
| 5 | GND | Ground pin. | |
| 6 | V _B | EL lamp drive. The lamp is connected in a high-voltage bridge circuit with V_B providing the complementary connection to V_A . The peak-to-peak AC voltage across the EL lamp thus two times V_{CS} . | |
| 7 | V _A | EL lamp drive. (See above) | |
| 8 | R _{EL-OSC} | The EL lamp oscillator frequency setting pin. The oscillator frequency is controlled by external resistor R _{EL} . | |

External Components

| External Component | Description and Selection Guide |
|--------------------------|---|
| Diode | Catch diode. A fast reverse recovery diode, with BV > 100, such as a 1N4148. |
| Capacitor C _S | This is the high voltage capacitor that stores the inductive energy transferred through the catch diode. A 100 volt capacitor between 10nF and 100nF is recommended. |
| Resistor R _{EL} | The EL lamp oscillator frequency setting resistor. This resistor, connected between the $R_{EL\text{-}OSC}$ pin and V_{DD} , provides an oscillator frequency inversely proportional to R_{EL} ; as R_{EL} increases, the EL lamp frequency decreases along with the current drawn by the lamp. Lamp color is also determined by this frequency. A $2M\Omega$ resistor between the $R_{EL\text{-}OSC}$ pin and the V_{DD} supply results in a lamp frequency around 350Hz: a $1M\Omega$ resistor will give $\approx\!700$ Hz. |
| Resistor R _{SW} | Switching Oscillator frequency setting resistor. The switching oscillator resistor is connected between the $R_{SW\text{-OSC}}$ pin and the V_{DD} supply. The switching frequency is inversely proportional to the resistor value, dropping as the resistance increases. |
| Inductor L | The inductor provides the voltage boost needed by means of inductive "flyback". The internal MOSFET switch alternately opens and closes the ground connection for the inductor at the L_X pin. When this internal switch opens, the inductor potential will forward-bias the catch diode and the current will pass through the storage capacitor C_S , charging it to a high voltage. |
| | Smaller inductors are preferred to prevent saturation. As the value of the inductor increases (and the series DC resistance of the inductor decreases), the switching frequency set by R _{SW} should be increased to prevent saturation. In general, smaller value inductors that can handle more current are more desirable when larger area EL lamps must be driven. |
| Lamp, R _{CL} | An external resistor (R_{CL}) in series with the lamp will protect the output drivers from high transient currents during lamp commutation. |

High Voltages Present


The IMP803 generates high voltages and caution should be exercised. $\,$



Application Information

Test and Application Circuit, 3.0V

Figure 1 shows the IMP803 configured to drive a 3-square-inch EL lamp, represented as a 10nF capacitor. With a 3.0V input, the EL lamp will be driven to moderate brightness.




- 1. Murata part # LQH4N561K04 (DC resistance <14.5 Ω)
- 2. Larger values may be required depending upon supply impedance.

803_09.eps

Figure 1. 3.0V Application

Test and Application Circuit, 5.0V

 $\it Figure~2$ shows a 5.0V input application driving a 6-square-inch EL lamp.



- 1. Murata part # LQH4N561K04 (DC resistance <14.5 Ω)
- 2. Larger values may be required depending upon supply impedance.


803_10.eps

Figure 2. 5.0V Application



Test and Application Circut, 6.0V

At higher input voltage levels, the IMP803 will drive large EL lamps. *Figure 3* shows a 6.0V circuit configuration that will drive a 10 square-inch lamp.



- 1. Murata part # LQH4N561K04 (DC resistance <14.5 Ω)
- 2. Larger values may be required depending upon supply impedance.


803_11.eps

Figure 3. 6.0V Application

Enable/Disable Operation

Figure 4 shows that the IMP803 can be enabled via a logic gate that connects R_{SW} to $V_{DD}\text{,}$ and disabled by connecting it to ground.

| Enable/Disable Table | | | |
|----------------------------|--------------|--|--|
| R _{SW} Connection | IMP803 State | | |
| V_{DD} | Enabled | | |
| GND | Disabled | | |



- 1. Murata part # LQH4N561K04 (DC resistance <14.5 Ω)
- 2. Larger values may be required depending upon supply impedance.

803_12.eps

Figure 4. Enable/Disable Operation



Dual Supply Operation with 1.5V Battery

The IMP803 can also be operate from a single battery cell when a regulated voltage higher than 2.0V is also available. This dual supply configuration, shown in *Figure 5*, uses the regulated voltage to operate the IMP803 while the energy for the high-voltage boost circuit comes from the battery.

The circuit of *Figure 5* thus allows operation with batteries that are below the 2V minimum specification or above the 6.0V maximum operating voltage.




Figure 5. Dual Supply Operation

Switch Resistance

The IMP803 inductor switch resistance is typically below 3.5 Ω , as shown in *Figure 6*.





Figure 6. Boost Switch On Resistance




Package Dimensions

SO (8-Pin)



MicroSO (8-Pin)



| Inches | | | Millimeters | | |
|--------|-------------|------------|-------------|------|--|
| | Min | Max | Min | Max | |
| | SO (8-Pin)* | | | | |
| Α | 0.053 | 0.069 | 1.35 | 1.75 | |
| A1 | 0.004 | 0.010 | 0.10 | 0.25 | |
| В | 0.013 | 0.020 | 0.33 | 0.51 | |
| С | 0.007 | 0.010 | 0.19 | 0.25 | |
| е | 0.0 | 50 | 1.3 | 27 | |
| Е | 0.150 | 0.157 | 3.80 | 4.00 | |
| Η | 0.228 | 0.244 | 5.80 | 6.20 | |
| L | 0.016 | 0.050 | 0.40 | 1.27 | |
| D | 0.189 | 0.197 | 4.80 | 2.00 | |
| | | MicroSO (8 | -Pin)** | | |
| Α | | 0.0433 | | 1.10 | |
| A1 | 0.0020 | 0.0059 | 0.050 | 0.15 | |
| A2 | 0.0295 | 0.0374 | 0.75 | 0.95 | |
| b | 0.0098 | 0.0157 | 0.25 | 0.40 | |
| С | 0.0051 | 0.0091 | 0.13 | 0.23 | |
| D | 0.1142 | 0.1220 | 2.90 | 3.10 | |
| е | 0.0256 BSC | | 0.65 BSC | | |
| Е | 0.193 BSC | | 4.90 BSC | | |
| E1 | 0.1142 | 0.1220 | 2.90 | 3.10 | |
| L | 0.0157 | 0.0276 | 0.40 | 0.70 | |
| а | 0° | 6° | 0° | 6° | |

^{*} JEDEC Drawing MS-012AA



ISO 9001 Registered

Daily Silver IMP Microelectronics Co.,Ltd 7 keda Road , Hi-Tech Park, NingBo,Zhejiang, P.R.C.

Post Code : 315040

Tel:(086)-574-87906358 Fax:(086)-574-87908866 e-mail:sales@ds-imp.com.cn Website:www.ds-imp.com.cn

^{**} JEDEC Drawing MO-187AA