

1N5400 thru 1N5408

General Purpose Plastic Rectifiers

Reverse Voltage 50 to 1000V Forward Current 3.0A

Feature

- * Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- * Construction utilizes void-free molded plastic technique
- * Low reverse leakage
- * High forward surge capability
- * Diffused junction
- * High temperature soldering guaranteed:
260°C/10 seconds, 0.375" (9.5mm) lead length,
5 lbs. (2.3kg) tension

Mechanical Data

Case: JEDEC DO-201AD, molded plastic body

Terminals: Plated axial leads, solderable per

MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.038 oz., 1.03 g

Handling precaution: None

Electrical Characteristic

1. Maximum & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter Symbol	symbol	1N 5400	1N 5401	1N 5402	1N 5403	1N 5404	1N 5405	1N 5406	1N 5407	1N 5408	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	300	400	500	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	210	280	350	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	300	400	500	600	800	1000	V
Maximum average forward rectified current 0.375" (9.5mm) lead length at $T_A = 75^\circ\text{C}$	$I_{F(AV)}$	3.0								A	
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	200								A	
Maximum full load reverse current, full cycle average, 0.375" (9.5mm) lead lengths at $T_A = 105^\circ\text{C}$	$I_{R(AV)}$	200								μA	
Typical thermal resistance (Note 1)	$R\theta J_A$	20								$^\circ\text{C/W}$	
Maximum DC blocking voltage temperature	T_A	150								$^\circ\text{C}$	
Operating junction and storage temperature range	T_J	-50 to +150								$^\circ\text{C}$	

Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter Symbol	symbol	1N 5400	1N 5401	1N 5402	1N 5403	1N 5404	1N 5405	1N 5406	1N 5407	1N 5408	Unit
Maximum instantaneous forward voltage at 3.0A	V_F	1.10								V	
Maximum DC reverse current $T_A = 25^\circ\text{C}$ at rated DC blocking voltage $T_A = 100^\circ\text{C}$	IR	5.0 200								μA	
Typical junction capacitance at 4.0V, 1MHz	C_J	30								PF	

NOTES:

1. Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted

1N5400 thru 1N5408

2. Characteristic Curves (TA = 25°C unless otherwise noted)

Fig. 1 - Forward Current Derating Curve




Fig 3. - Typical Instantaneous Forward Characteristics




Fig 5. - typical transient thermal impedance




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current




Fig 4. - Typical Reverse Characteristics






Fig 6. - Typical Junction Capacitance



1N5400 thru 1N5408

3. dimension:

Package outline



Dimensions				Note: DO-201AD molded plastic case The marking band indicates the cathode
	inches		mm	
	Min.	Max.	Min.	Max.
L	0.335	0.375	8.5	9.5
L1	1.0	-	25.4	-
ΦD	0.197	0.220	5.0	5.6
Φd	0.048	0.052	1.2	1.3