

Wire-wound Chip Power Inductors (CB series)

CBC3225T2R2MR



■ Features

- Item Summary
2.2uH±20%, 1.13A, 1210/3225 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 1000pcs

■ Products characteristics table

Inductance	2.2 uH ± 20 %
Case Size (EIA/JIS)	1210/3225
Rated Current (max)	1.13 A
Saturation Current (max)	2 A
Temperature Rise Current (max)	1.13 A
DC Resistance (max)	104 mΩ
DC Resistance (typ)	80 mΩ
LQ Measuring Frequency	0.1 MHz
Self Resonant Frequency (min)	190 MHz
Operating Temp. Range	-40 to +105 °C (Including-self-generated heat)
Temperature characteristic (Inductance change)	± 20 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	3.2 ±0.2 mm
Dimension W	2.5 ±0.2 mm
Dimension T	2.5 ±0.2 mm
Dimension e	0.6 ±0.3 mm

2017.01.02

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.




Wire-wound Chip Power Inductors (CB series)

CBC3225T2R2MR



Dimension	unit : mm	unit : inch
Length :	3.2 +/- 0.2	(0.126 +/- 0.008)
Width :	2.5 +/- 0.2	(0.098 +/- 0.008)
Height :	2.5 +/- 0.2	(0.098 +/- 0.008)

Inductance :	2.2	uH (test freq at 0.1MHz)
DC Resistance :	0.08 / 0.104	ohm (typ / max)
Saturation Current :	2,000	mA (max)
Temp. rise Current :	1,130	mA (max)
Saturation current typical : 30% reduction from initial L value.		
Temp rise Current typical : Temperature will rise by 40 deg C		



The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the data at any time without notice. Before making final selection, please check product specification.