


# Multilayer Chip Inductor for Choke – MCL-A Series

Operating Temp. : -40°C~+85°C



## FEATURES

- Monolithic structure for high reliability
- Excellent solderability and high heat resistance
- No cross coupling due to magnetic shield
- High DC bias current due to developed material
- Low DC resistance


## APPLICATIONS

- DC-DC converter circuits for mobile phones, wearable devices, DVCs, HDDs, etc.

## PRODUCT IDENTIFICATION

<u>MCL</u>	<u>2012</u>	<u>A</u>	<u>2R2</u>	<u>M</u>	<u>T</u>																				
①	②	③	④	⑤	⑥																				
①	②		③		⑥																				
<table border="1"> <tr><th colspan="2">Type</th></tr> <tr><td>MCL</td><td>Chip Inductor for Choke</td></tr> </table>	Type		MCL	Chip Inductor for Choke	<table border="1"> <tr><th colspan="2">External Dimensions (L×W) (mm)</th></tr> <tr><td>2012 [0805]</td><td>2.0×1.25</td></tr> <tr><td>2016 [0806]</td><td>2.0×1.6</td></tr> <tr><td>2520 [1008]</td><td>2.5×2.0</td></tr> </table>		External Dimensions (L×W) (mm)		2012 [0805]	2.0×1.25	2016 [0806]	2.0×1.6	2520 [1008]	2.5×2.0	<table border="1"> <tr><th colspan="2">Feature Type</th></tr> <tr><td>A</td><td>Inner Code</td></tr> </table>		Feature Type		A	Inner Code	<table border="1"> <tr><th colspan="2">Packing</th></tr> <tr><td>T</td><td>Tape &amp; Reel</td></tr> </table>	Packing		T	Tape & Reel
Type																									
MCL	Chip Inductor for Choke																								
External Dimensions (L×W) (mm)																									
2012 [0805]	2.0×1.25																								
2016 [0806]	2.0×1.6																								
2520 [1008]	2.5×2.0																								
Feature Type																									
A	Inner Code																								
Packing																									
T	Tape & Reel																								
④	⑤		⑥																						
<table border="1"> <tr><th colspan="2">Nominal Inductance</th></tr> <tr><td>Example</td><td>Nominal Value</td></tr> <tr><td>2R2</td><td>2.2μH</td></tr> </table>	Nominal Inductance		Example	Nominal Value	2R2	2.2μH	<table border="1"> <tr><th colspan="2">Inductance Tolerance</th></tr> <tr><td>M</td><td>±20%</td></tr> </table>		Inductance Tolerance		M	±20%	<table border="1"> <tr><th colspan="2">Packing</th></tr> <tr><td>T</td><td>Tape &amp; Reel</td></tr> </table>		Packing		T	Tape & Reel							
Nominal Inductance																									
Example	Nominal Value																								
2R2	2.2μH																								
Inductance Tolerance																									
M	±20%																								
Packing																									
T	Tape & Reel																								

## SHAPE AND DIMENSIONS



Unit: mm [inch]

Type	L	W	T	a
MCL2012 [0805]	2.0 (+0.3, -0.1) [.079 (+.012, -.004)]	1.25±0.2 [.049±.008]	0.85±0.2 [.033±.008]	0.5±0.3 [.020±.012]
MCL2016 [0806]	2.0 (+0.3, -0.1) [.079 (+.012, -.004)]	1.6±0.2 [.063±.008]	0.9±0.1 [.035±.004]	0.5±0.3 [.020±.012]
MCL2520 [1008]	2.5±0.2 [.098±.008]	2.0(+0.3, -0.1) [.079(+.012, -.004)]	0.9±0.1 [.035±.004]	0.5±0.3 [.020±.012]

## SPECIFICATIONS

### MCL2012A TYPE

Part Number	Inductance	L Test Freq. L	DC Resistance	Min. Self-resonant Frequency	Saturation Current Typ.	Heat Rating Current Max.
Units	μH	MHz	Ω	MHz	mA	mA
Symbol	L	Freq.	DCR	S.R.F	Isat	Irms
MCL2012A2R2MT	2.2	1	0.18±25%	50	300	1300
MCL2012A4R7MT	4.7	1	0.30±25%	60	180	850

### MCL2016A TYPE

Part Number	Inductance	L Test Freq. L	DC Resistance	Min. Self-resonant Frequency	Saturation Current Typ.	Heat Rating Current Max.
Units	μH	MHz	Ω	MHz	mA	mA
Symbol	L	Freq.	DCR	S.R.F	Isat	Irms
MCL2016A1R0MT	1.0	1	0.14±25%	120	900	1100
MCL2016A2R2MT	2.2	1	0.22±25%	70	600	850

### MCL2520A TYPE

Part Number	Inductance	L Test Freq. L	DC Resistance	Min. Self-resonant Frequency	Saturation Current Typ.	Heat Rating Current Max.
Units	μH	MHz	Ω	MHz	mA	mA
Symbol	L	Freq.	DCR	S.R.F	Isat	Irms
MCL2520A2R2MT	2.2	1	0.13±25%	70	500	1400
MCL2520A4R7MT	4.7	1	0.28±25%	45	250	950

※Rated current: Isat or Irms, whichever is smaller;

※Isat: DC current at which the inductance drops approximate 30% from its value without current;

※Irms : DC current that causes the temperature rise ( $\Delta T = 40^{\circ}\text{C}$ ) from  $20^{\circ}\text{C}$  ambient.