

DATASHEET

1.9mm Round Subminiature "Gull Wing" Lead Infrared LED IR91-21C/TR7



Features

- Small double-end package
- High reliability
- Low forward voltage
- Good spectral matching to Si photodetector
- Pb free
- The product itself will remain within RoHS compliant version.

Descriptions

IR91-21C/TR7 is an infrared emitting diode in miniature

SMD package which is molded in a water clear plastic with spherical top view lens.

The device is spectrally matched with silicon photodiode and phototransistor.

Applications

- PCB mounted infrared sensor
- Infrared emitting for miniature light barrier
- Floppy disk drive
- Optoelectronic switch
- Smoke detector

Device Selection Guide

Part Category	Chip Material	Lens Color	
IR	GaAlAs	Water Clear	

Revision

: 3

www.everlight.com


Release Date: 2013-06-03 17:41:55.0


Copyright © 2013, Everlight All Rights Reserved. Release Date :5/30/2013. Issue No:DIR-0000946 Rev

LifecyclePhase: 正式發行 Expired Period: Forever



Package Dimensions





- Cathode
- ② Anode

Notes: 1.All dimensions are in millimeters

2.Tolerances unless dimensions ±0.1mm

2

www.everlight.com

 $Copyright © 2013, Everlight All Rights Reserved. \ Release \ Date: 5/30/2013. \ Issue \ No: DIR-0000946 \quad Rev \ 3$

Revision : 3 LifecyclePhase: Approved

Expired Period: Forever

Release Date: 2013-06-03 17:41:55.0



Absolute Maximum Ratings (Ta=25)

Parameter	Symbol	Rating	Units
Continuous Forward Current	I_{F}	65	mA
Reverse Voltage	V_R	5	V
Operating Temperature	T_{opr}	-25 ~ +85	
Storage Temperature	T_{stg}	-40 ~ +85	
Soldering Temperature *1	T_{sol}	260	
Power Dissipation at(or below)	P_d	130	mW
25 Free Air Temperature			

Notes: *1: Soldering time 5 seconds.

Electro-Optical Characteristics (Ta=25)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Units
		I _F =20mA	3.0	5.0	<u>_</u>	
Radiant Intensity	$I_{\rm E}$	$I_F \!\!=\!\! 100 mA$ Pulse Width 100 μ s ,Duty 1%	7-7	25	-	mW /sr
Peak Wavelength	p	I _F =20mA		940		nm
Spectral Bandwidth		I _F =20mA	-	45		nm
Forward Voltage	V_{F}	$I_F=20mA$		1.2	1.5	V
Reverse Current	I_R	V _R =5V			10	μA
View Angle	2 1/2	I _F =20mA		25		deg

3

Revision

: 3

Release Date:2013-06-03 17:41:55.0

www.everlight.com

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3

LifecyclePhase: Expired Period: Forever Expired Period: Forever



Typical Electro-Optical Characteristics Curves

Fig.1 Forward Current vs.

Ambient Temperature




Fig.2 Spectral Distribution




Fig.3 Forward Current





Fig.4 Relative Intensity vs.



4

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3

www.everlight.com

Revision : 3 Release Date:2013-06-03 17:41:55.0


LifecyclePhase: Approved Expired Period: Forever



Typical Electro-Optical Characteristics Curves

Fig.5 Relative Radiant Intensity vs.

Angular Displacement



5

Revision

: 3

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3

www.everlight.com

LifecyclePhase: 正式發行 Approved

Expired Period: Forever




Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package: The LEDs should be kept at 30 or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life is 168 hours under 30 or less and 60% RH or less.

 If unused LEDs remain, it should be stored in moisture proof packages.
 - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.Baking treatment: 60±5 for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3

3.4 After soldering, do not warp the circuit board.

6

Revision

www.everlight.com

Release Date:2013-06-03 17:41:55.0

Expired Period: Forever

LifecyclePhase: Approved

: 3




4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



7

Revision

: 3

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3


www.everlight.com

Release Date: 2013-06-03 17:41:55.0

LifecyclePhase: Expired Period: Forever Expired Period: Forever




Package Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Carrier Tape Dimensions:Loaded quantity 1000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

8

Revision

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3


www.everlight.com

: 3 LifecyclePhase:

Expired Period: Forever



Label Form Specification



CPN: Customer's Production Number

P/N : Production Number QTY: Packing Quantity

CAT: Ranks

HUE: Peak Wavelength

REF: Reference

LOT No: Lot Number

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD. Office: No. 6-8, Zhonghua Rd., Shulin Dist.,

New Taipei City 23860, Taiwan

Tel: 886-2-2685-6688

Fax: 886-2685-2699, 6897 http://www.everlight.com

9

www.everlight.com

Copyright © 2013, Everlight All Rights Reserved. Release Date : 5/30/2013. Issue No: DIR-0000946 Rev 3

Revision : 3

Release Date:2013-06-03 17:41:55.0

LifecyclePhase: Approved Expired Period: Forever