
Spec Sheet

SMD Power Inductors (NR series H type)

NRH3012T100MN



Features

- Item Summary
 10uH±20%, 0.72A, 3.0x3.0x1.2mm
- Lifecycle Stage
 - Mass Production
- Standard packaging quantity (minimum)
 Taping Embossed 2000pcs


Products characteristics table

10 uH ± 20 %
3.0x3.0
0.72 A
0.73 A
0.78 A
0.72 A
0.85 A
0.324 Ω
0.27 Ω
100 kHz
32 MHz
-25 to +120 ℃ (Including-self-generated heat)
± 20 %
Yes
Yes
Reflow

External Dimensions

Dimension L	3.0 ±0.1 mm
Dimension W	3.0 ±0.1 mm
Dimension H	Max 1.2 mm
Dimension e	0.9 ±0.2 mm
Dimension f	1.9 ±0.2 mm

Recommended Land Patterns



2017.01.02

SMD Power Inductors (NR series H type)

NRH3012T100MN



Dimension unit : mm unit: inch Length: 3.0 + / - 0.1(0.118 + / - 0.004)Width: 3.0 +/- 0.1 (0.118 + / - 0.004)max.) Height: 1.2 (0.047 max.

Inductance: 10 (test freq at 0.1MHz) иΗ DC Resistance: 0.27 / 0.324 ohm (typ/max)

Saturation Current: 730 mA (max) 720 mA (max) Temp. rise Current:

> Saturation current typical: 30% reduction from initial L value. Temp rise Current typical: Temperature will rise by 40 deg C

