

N-Channel MOSFET MEM2302M3


General Description

MEM2302M3G Series N-channel enhancement mode field-effect transistor, produced with high cell density DMOS trench technology, which is especially used to minimize on-state resistance. This device particularly suits low voltage applications, and low power dissipation in a very small outline surface mount package.

Features

- 20V/3A
 $R_{DS(ON)} = 29m\Omega @ V_{GS} = 4.5V, I_D = 3A$
 $R_{DS(ON)} = 36m\Omega @ V_{GS} = 2.5V, I_D = 2A$
- High Density Cell Design For Ultra Low On-Resistance
- Subminiature surface mount package: SOT23-3L

Pin Configuration



Typical Application

- Battery management
- High speed switch
- Low power DC to DC converter

Absolute Maximum Ratings

Parameter		Symbol	Ratings	Unit
Drain-Source Voltage		V_{DSS}	20V	V
Gate-Source Voltage		V_{GSS}	± 8	V
Drain Current	$T_A = 25^\circ C$	I_D	3	A
	$T_A = 70^\circ C$		2	
Pulsed Drain Current ^{1,2}		I_{DM}	15	A
Total Power Dissipation	$T_A = 25^\circ C$	Pd	0.7	W
	$T_A = 70^\circ C$		0.46	
operating junction temperature		T_j	150	$^\circ C$
Storage Temperature Range		T_{stg}	-65/150	$^\circ C$

Thermal Characteristics

Parameter	Symbol	Ratings	Unit
Thermal Resistance, Junction-to-Ambient	R θ JA	140	°C/W

Electrical Characteristics





MEM2302M3







Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} =0V, I _D =250uA	20	23		V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250uA	0.51	0.53	0.85	V
Gate-Body Leakage	I _{GSS}	V _{DS} =0V, V _{GS} =8V		1.6	100	nA
		V _{DS} =0V, V _{GS} =-8V		-0.2	-100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =20V V _{GS} =0V		6.3	1000	nA
Static Drain-Source On-Resistance	R _{DS(ON)}	V _{GS} =4.5V, I _D =3A		29	50	m Ω
		V _{GS} =2.5V, I _D =2A		36	65	m Ω
Forward Transconductance	g _{FS}	V _{DS} = 5 V, I _D = 3.6A		8		S
Source-drain (diode forward) voltage	V _{SD}	V _{GS} =0V, I _D =1.25A	0.4	0.7	1	V
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{DS} = 10 V, V _{GS} = 0 V, f = 1 MHz		300		pF
Output Capacitance	C _{oss}			120		
Reverse Transfer Capacitance	C _{rss}			80		
Switching Characteristics						
Turn-On Delay Time	td(on)	V _{DD} = 15 V, R _L = 2.8 Ω I _D =3.6A V _{GEN} = 4.5V, R _g = 36 Ω		8	15	ns
Rise Time	tr			50	80	
Turn-Off Delay Time	td(off)			15	60	
Fall-Time	tf			10	25	
Total Gate Charge	Q _g	V _{DS} = 10V, V _{GS} = 4.5 V, I _D = 3.6A		4	10	nC
Gate-Source Charge	Q _{gs}			0.65		
Gate-Drain Charge	Q _{gd}			1.5		


1、Repetitive rating, pulse width limited by junction temperature.

2、Pulse width <300us , duty cycle <0.5%.


Typical Performance Characteristics







Package Information



- The information described herein is subject to change without notice.
- Nanjing Micro One Electronics Inc is not responsible for any problems caused by circuits or diagrams described herein whose related industrial properties, patents, or other rights belong to third parties. The application circuit examples explain typical applications of the products, and do not guarantee the success of any specific mass-production design.
- Use of the information described herein for other purposes and/or reproduction or copying without the express permission of Nanjing Micro One Electronics Inc is strictly prohibited.
- The products described herein cannot be used as part of any device or equipment affecting the human body, such as exercise equipment, medical equipment, security systems, gas equipment, or any apparatus installed in airplanes and other vehicles, without prior written permission of Nanjing Micro One Electronics Inc.
- Although Nanjing Micro One Electronics Inc exerts the greatest possible effort to ensure high quality and reliability, the failure or malfunction of semiconductor products may occur. The user of these products should therefore give thorough consideration to safety design, including redundancy, fire-prevention measures, and malfunction prevention, to prevent any accidents, fires, or community damage that may ensue.