

DUAL OPERATIONAL AMPLIFIER AND REFERENCE REGULATOR


GENERAL DESCRIPTION

The **FP103**, a 1-chip composed of one independent op-amp (OPA2) and another op-amp (OPA1) with a 2.5V precision voltage reference on non-inverting input, applied to offer space and low cost in many applications such as the secondary feedback control of power supply, DC/DC converter or adaptor.


Using few external components, **FP103**, a high performance integrated IC, is designed for a feedback circuit. The circuit diagram of the typical application example is as below.

FEATURES

- Fixed Reference Voltage: 2.5V
- Reference Voltage Precision: 1%
- Output sink current up to 100mA
- Low quiescent supply current
- Wide operating voltage range: 3~32V(+/-16V)
- Low input offset voltage
- Unit gain bandwidth: 0.9MHz
- Package: PDIP8/SOP8






SOP8



PDIP8

TYPICAL APPLICATION CIRCUIT




FUNCTIONAL BLOCK DIAGRAM

MARK VIEW

PIN DESCRIPTION

| NAME | NO. | STATUS | DESCRIPTION |
|------|-----|--------|--------------------------------------|
| VO1 | 1 | O | OPA1 Output |
| VI1 | 2 | I | OPA1 Inverting Input |
| VNI1 | 3 | I | OPA1 Non-inverting Input |
| VEE | 4 | P | IC Ground or Negative Supply Voltage |
| VNI2 | 5 | I | OPA2 Non-inverting Input |
| VI2 | 6 | I | OPA2 Inverting Input |
| VO2 | 7 | O | OPA2 Output |
| VCC | 8 | P | Positive Supply Voltage |

ORDER INFORMATION

| Part Number | Operating Temperature | Package | Description |
|-------------|-----------------------|---------|-------------|
| FP103P-LF | -20°C~85°C | PDIP8 | Tube |
| FP103D-LF | -20°C~85°C | SOP8 | Tube |
| FP103DR-LF | -20°C~85°C | SOP8 | Tape & Reel |

IC DATE CODE DISTINGUISH

FOR EXAMPLE:

| | |
|----------|---|
| January | A (Front Half Month), B (Last Half Month) |
| February | C, D |
| March | E, F -----And so on |

Lot Number is the last two numbers


For Example:

A3311C62

→ Lot Number

ABSOLUTE MAXIMUM RATINGS

| | |
|---|---------------------|
| Supply Voltage (V _{cc}) ----- | + 3 6 V |
| Differential Input Voltage (V _{id}) ----- | + 3 6 V |
| Input Voltage (V _i) ----- | -0.3 ~+36V |
| Maximum Junction Temperature (T _j) ----- | 150 °C |
| Thermal Resistance Junction to Ambient (SOP package) | 175°C/W |
| (PDIP package) ----- | 100°C/W |
| Power Dissipation (SOP8 package) | |
| Ta=25°C ----- | 650mW |
| Ta=70°C ----- | 550mW |
| Operating Temperature Range (T _{min} ~ T _{max.}) ----- | -20°C ~ 85°C |
| Storage Temperature Range ----- | - 6 5 °C ~ 1 5 0 °C |
| SOP8 Lead Temperature (soldering, 10 sec) ----- | +260°C |
| PDIP8 Lead Temperature (soldering, 20 sec) ----- | +260°C |


IR-REFLOW

DC ELECTRICAL CHARACTERISTICS
Operating Amplifier1

| PARAMETER | SYMBOL | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-------------------------------------|--------------|--|----------|------|----------|------------------|
| Input Offset Voltage | V_{io} | FP103, $T_{amb}=25^\circ C$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 1 | 4 5 | mV |
| Input Offset Voltage Drift | DV_{io} | $T_{amb}=25^\circ C$ | | 7 | | $\mu V/^\circ C$ |
| Input Bias Current (negative input) | I_{ib} | $T_{amb}=25^\circ C$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 20 | | nA |
| Large Signal Voltage Gain | A_{vd} | $V_{icm}=0V$ $V_{CC}=15V, R_L=2K$ | | 100 | | V/mV |
| Supply Voltage Rejection Ratio | SVR | $V_{icm}=0V$ $V_{CC}=5V$ to $30V$ | 65 | 100 | | dB |
| Output Current Source | I_{source} | $V_{CC} = +15V$ $V_O=2V, V_{id}=+1V$ | 30 | 50 | | mA |
| Short Circuit to Ground | I_o | $V_{CC}=+15V$ | | 50 | 70 | mA |
| Output Current Sink | I_{sink} | $V_{id}=-1V$ $V_{CC}=+15V, V_O=2V$ | 8 | 10 | | mA |
| High Level Output Voltage | V_{OH} | $V_{CC}^+=30V$ $T_{amb}=25^\circ C, R_L=10K$ $T_{min} \leq T_{amb} \leq T_{max}$ | 27 27 | 28 | | V |
| Low Level Output Voltage | V_{OL} | $R_L=10K$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 3 | 20 20 | mV |
| Slew Rate at Unity Gain | SR | $V_i=0.5$ to $2V$, $V_{CC}=15V$ $R_L=2K, C_L=100pF$ Unity Gain | 0.2 | 0.4 | | $V/\mu s$ |
| Gain Bandwidth Product | GBP | $V_{CC}=30V$, $R_L=2K$ $C_L=100pF, f=100kHz$, $V_{in}=10 mV$ | 0.5 | 0.9 | | MHz |
| Total Harmonic Distortion | THD | $f=1kHz, A_V=20dB$ $R_L=2K, V_{CC}=30V$ $C_L=100pF, V_O=2V_{PP}$ | | 0.02 | | % |

DC ELECTRICAL CHARACTERISTICS (Cont.)
Operating Amplifier2

| PARAMETER | SYMBOL | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---------------------------------|--------------|---|----------|------|--------------------------------|---------------------|
| Input Offset Voltage | V_{io} | $FP103, T_{amb}=25^{\circ}C$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 1 | 4 5 | mV |
| Input Offset Voltage Drift | DV_{io} | $T_{amb}=25^{\circ}C$ | | 7 | | $\mu V/{}^{\circ}C$ |
| Input Offset Current | I_{io} | $T_{amb}=25^{\circ}C$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 2 | 30 50 | nA |
| Input Bias Current | I_{ib} | $T_{amb}=25^{\circ}C$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 20 | 150 200 | nA |
| Large Signal Voltage Gain | A_{vd} | $V_{CC}=15V, R_L=2K,$ $V_O=1.4V$ to $11.4V$ $T_{min} \leq T_{amb} \leq T_{max}$ | 50 25 | 100 | | V/mV |
| Supply Voltage Rejection Ratio | SVR | $V_{CC}=5V$ to $30V$ | 65 | 100 | | dB |
| Input Common Mode Voltage Range | V_{icm} | $V_{CC}=+30V$ $T_{min} \leq T_{amb} \leq T_{max}$ | 0 0 | | $(V_{CC})-1.5$ $(V_{CC})-2$ | V |
| Common Mode Rejection Ratio | CMRR | $T_{amb}=25^{\circ}C$ $T_{min} \leq T_{amb} \leq T_{max}$ | 70 60 | 85 | | dB |
| Output Current Source | I_{source} | $V_{CC}=+15V,$ $V_O=2V, V_{id}=+1V$ | 30 | 50 | | mA |
| Short Circuit to Ground | I_o | $V_{CC}=+15V,$ | | 50 | 70 | mA |
| Output Current Sink | I_{sink} | $V_{id}=-1V,$ $V_{CC}=+15V, V_O=2V$ | 7 | 10 | | mA |
| High Level Output Voltage | V_{OH} | $V_{CC}^{+}=30V$ $T_{amb}=25^{\circ}C, R_L=10K$ $T_{min} \leq T_{amb} \leq T_{max}$ | 27 27 | 28 | | V |
| Low Level Output Voltage | V_{OL} | $R_L=10K$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 3 | 20 20 | mV |
| Slew Rate at Unity Gain | SR | $V_i=0.5$ to $3V, V_{CC}=15V$ $R_L=2K, C_L=100pF,$ Unity Gain | 0.2 | 0.4 | | $V/\mu S$ |
| Gain Bandwidth Product | GBP | $V_{CC}=30V, R_L=2K$ $C_L=100pF, f=100kHz,$ $V_{in}=10mV$ | 0.5 | 0.9 | | MHz |
| Total Harmonic Distortion | THD | $f=1kHz, A_v=20dB$ $R_L=2K, V_{CC}=30V$ $C_L=100pF, V_O=2V_{PP}$ | | 0.02 | | % |

DC ELECTRICAL CHARACTERISTICS (Cont.)
Voltage Reference







| PARAMETER | SYMBOL | VALUE | UNIT |
|-----------------|--------|----------|------|
| Cathode Current | I_k | 1 to 100 | mA |



| PARAMETER | SYMBOL | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|--|------------------|---|----------------|-----|----------------|----------|
| Reference Input Voltage | V_{ref} | FP103, $T_{amb}=25^\circ C$ $T_{min} \leq T_{amb} \leq T_{max}$ | 2.475 2.450 | 2.5 | 2.525 2.550 | V |
| Reference Input Voltage Deviation Over Temperature Range | ΔV_{ref} | $V_{KA}=V_{ref}; I_k=10mA$ $T_{min} \leq T_{amb} \leq T_{max}$ | | 7 | 30 | mV |
| Minimum Cathode Current for Regulation | I_{min} | $V_{KA}=V_{ref}$ | | 0.2 | 1 | mA |
| Dynamic Impedance (note 1) | $ Z_{KA} $ | $V_{KA}=V_{ref}, \Delta I_k=1 \text{ to } 100mA,$ $f < 1KHz, \text{note1}$ | | 0.2 | 0.5 | Ω |


1.The dynamic impedance is defined as $Z_{KA}=\Delta V_{KA}/\Delta I_k$

Total Supply Current

| PARAMETER | SYMBOL | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|--|----------|---|-----|-----|----------|------|
| Total Supply Current, excluding Current in the Voltage Reference | I_{cc} | $V_{CC+}=5V, \text{no load}$ $T_{min} < T_{amb} < T_{max}$ $V_{CC+}=30V, \text{no load}$ $T_{min} < T_{amb} < T_{max}$ | | 0.7 | 1.2 2 | mA |

TYPICAL CHARACTERISTICS


TYPICAL CHARACTERISTICS (Cont.)



PACKAGE OUTLINE
SOP 8


| SYMBOLS | MIN | MAX |
|----------------|-------|-------|
| A | 0.053 | 0.069 |
| A1 | 0.004 | 0.010 |
| D | 0.189 | 0.196 |
| E | 0.150 | 0.157 |
| H | 0.228 | 0.244 |
| L | 0.016 | 0.050 |
| θ° | 0 | 8 |

UNIT:INCH

NOTE:

1. JEDEC OUTLINE:MS-012 AA
2. DIMENSIONS "D" DOES NOT INCLUDE MOLD FLASH,PROTRUSIONS OR GATE BURRS.MOLD FLASH,PROTRUSIONS AND GATE BURRS SHALL NOT EXCEED .15mm (.06in) PER SIDE
3. DIMENSIONS "E" DOES NOT INCLUDE INTER-LEAD FLASH,OR PROTRUSIONS. INTER-LEAD FLASH AND PROTRUSIONS SHALL NOT EXCEED .25mm (.10in) PER SIDE.

PDIP 8


| SYMBOLS | MIN | NOR | MAX |
|----------------|----------|-------|-------|
| A | - | - | 0.210 |
| A1 | 0.015 | - | - |
| A2 | 0.125 | 0.130 | 0.135 |
| D | 0.355 | 0.365 | 0.400 |
| E | 0.300BSC | | |
| E1 | 0.245 | 0.250 | 0.255 |
| L | 0.115 | 0.130 | 0.150 |
| e _θ | 0.335 | 0.355 | 0.375 |
| Θ° | 0 | 7 | 15 |

UNIT:INCH


Note:

4. JEDEC OUTLINE:MS-001 BA
5. "D""E1"DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED .010 INCH
6. eB IS MEASURED AT THE LEAD TIPS WITH THE LEADS UNCONSTRAINED POINTED OR ROUNDED LEAD TIPS ARE PREFERRED TO EASE INSERTION
7. DISTANCE BETWEEN LEADS INCLUDING DAM BAR PROTRUSIONS TO BE .005 INCH MINIMUM
8. DATUM PLANE H CONINCIDENT WITH THE BOTTOM OF LEAD, WHERE LEAD EXITS BODY.


PACKING SPECIFICATIONS

BOX DIMENSION

TUBE INSIDE BOX AND CARTON



TAPE & REEL INSIDE BOX AND CARTON



PACKING QUANTITY SPECIFICATIONS

| | |
|-------------------------|-------------------------|
| 100 EA / TUBE | 2500 EA / REEL |
| 100 TUBES / INSIDE BOX | 4 INSIDE BOXES / CARTON |
| 4 INSIDE BOXES / CARTON | |

LABEL SPECIFICATIONS

TAPPING & REEL

Feeling Technology Corp.
Product FP103
Lot No A3311C62
D/C 4Xx-XXL
Q'ty ◎~◎

無鉛
Lead Free

CARTON

Feeling Technology Corp.




Product Type: FP103
Lot No: A3311C62
Date Code: 4Xx-XXL
Package Type: SOP-8L
Marking Type: Laser
Total Q'ty: 10,000

無鉛
Lead Free

CARRIER TAPE DIMENSIONS

| APPLICATION | W | P | E | F | D | D ₁ |
|-------------|---|---------|----------|---------|----------|----------------------|
| SOP8 | 12.0 ^{+0.3} _{-0.1} | 8.0±0.1 | 1.75±0.1 | 5.5±0.1 | 1.55±0.1 | 1.5 ^{+0.25} |

| APPLICATION | P ₀ | P ₁ | A ₀ | B ₀ | K ₀ | t |
|-------------|----------------|----------------|----------------|----------------|----------------|------------|
| SOP8 | 4.0±0.1 | 2.0±0.1 | 6.4±0.1 | 5.20±0.1 | 2.1±0.10 | 0.30±0.013 |


REEL DIMENISONS


| APPLICATION | MATERIAL | A | B | C | D | T ₁ | T ₂ |
|-------------|--------------|---------|--------|------------|-------|----------------|----------------|
| SOP8 | PLASTIC REEL | 330±0.1 | 62±1.5 | 12.75+0.15 | 2+0.6 | 12.4+0.2 | 2.0+0.2 |