


# 6.2mm Square Type with Middle-travel (Surface Mount) SKRA Series


Part number		SKRAAKE010
Туре		Surface mount
Operating force		2.45N
Operating direction		Top push
Travel		0.3mm
Operating life (5mA 5V DC)		100,000 cycles
Initial contact resistance		100m $\Omega$ max.
Protective structure		IP67 equivalent
Stem color		White
Series type		Sharp feeling type
Operating temperature range		-30℃ to +85℃
Rating (max.)		50mA 12V DC
Rating (min.)		10μA 1V DC
Electrical	Insulation resistance	100M $\Omega$ min. 100V DC for 1min.
performance	Voltage proof	250V AC for 1 min.
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively
Environmental performance	Cold	-30±2℃ for 96h
	Dry heat	80±2℃ for 96h
	Damp heat	60±2℃, 90 to 95%RH for 96h

Minimum order unit	Japan	3,000
(pcs.)		
	Export	3,000


## Photo



## Dimensions




## Land Dimensions




Viewed from mounting face.

## Circuit Diagram



## **Packing Specifications**

#### **Taping**



Number of packages 1 reel 3,000 (pcs.)

1 case / Japan 30,000

	1 case / export packing	30,000
Reel width W(mm)		13.5
Tape width (mm)		12
Export package mea	asurements (mm)	395×395×205

### Soldering Conditions

#### **Condition for Reflow**


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2  $\Phi$  CA(K) or CC(T) at solder joints (copper foil surface). A heat resisting tape should be used for fix measurement.

3. Temperature profile



- (1) The above temperature shall be measured of the top of switch. There are cases where PC board's temperature greatly differs from that of the switch, depending on the material, size, thickness of PC board's and others. Care, should be taken to prevent the switch's surface temperature from exceeding  $260^{\circ}$ C.
- (2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

#### **Manual Soldering**

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

- 1. Consult with us for availability of TACT switch™ washing.
- 2. Prevent flux penetration from the top side of the TACT switch™.
- 3. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 4. The second soldering should be done after the switch returns to normal temperature.

#### Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders for taping products per minimum order unit (1 reel or a case).
- 3. For  $\phi$ 330mm diameter reel requirements, please contact us.
- 4. This products can be used in vehicles.
  - Although these products are designed to perform over a wide operating temperature range, please ensure that you receive and read the formal delivery specifications before use.
- 5. Protective structure:
  - Assumes the switch is left alone without being operated. Under the specified conditions, dust and water ingress with a significant impact on the switch's on-off function is prevented.
  - IP67 dust and water resistance is guaranteed for the switch alone and performance may not be guaranteed depending on the mounting conditions and usage.